


Parts Information: **Rotary Hammer Drill SDS Plus 26mm** 900Ŵ/230V **Model No: SDSPLUS26**



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. There may be alternative versions of this product, please contact us should you require this information. IMPORTANT: No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR I.B 01284 757500 01284 703534 sales@sealey.co.uk

💮 www.sealey.co.uk



Parts Information: **Rotary Hammer Drill SDS Plus 26mm** 900Ŵ/230V **Model No: SDSPLUS26**

	SDSPLUS26.01				Description
2	3D3FL0320.01	Front Cover	46	SDSPLUS26.46	C-Ring 12.5 x 1mm
	SDSPLUS26.02	Steel Ball Rack	47	SDSPLUS26.47	Safety Clutch Plate (B)
3	SDSPLUS26.03	Steel Ball Rack Ring	48	SDSPLUS26.48	Safety Clutch Internal Spring
4	SDSPLUS26.04	Steel Ball Rack Spring	49	SDSPLUS26.49	Safety Clutch External Spring
5	SDSPLUS26.05	Self-Tapping Screw 4.8 x 25-F	50	SDSPLUS26.50	Safety Clutch Spring Seat
6	SDSPLUS26.06	Front Casing	51	SDSPLUS26.51	C-Ring 8.8 x 1mm
7	SDSPLUS26.07	Oil Seal	52	B/627ZZ	Bearing 627ZZ
8	SDSPLUS26.08	C-Ring 26.7 x 1.6mm	53	SDSPLUS26.53	Middle Cover
9	SDSPLUS26.09	Bearing 61906	54	SDSPLUS26.54	Rubber Pin
10	SDSPLUS26.10	C-Ring 47mm	55	SB-4.0	Steel ball 4.0mm
11	SB-7.0	Steel Ball 7.0mm	56	SDSPLUS26.56	Function Knob
12	SDSPLUS26.12	Rotary Sleeve	57	B/6000-2RS	Bearing 6000-2rs
13	SB-6.4	Steel ball 6.4mm	58	SDSPLUS26.58	Rotor
14	SDSPLUS26.14	O-Ring 19.8 x 2mm	59	B/608ZZ	Bearing 608zz
15	SDSPLUS26.15	O-Ring 11 x 2mm	60	SDSPLUS26.60	Guide Ring
16	SDSPLUS26.16	Impact Hammer	61	SDSPLUS26.61	Stator
17	SDSPLUS26.17	Cylinder	62	SDSPLUS26.62	Self-Tapping Screw 4 x 55mm
18	SDSPLUS26.18	Cylinder Key A3 x 3 x 18	63	SDSPLUS26.63	Housing
19	SDSPLUS26.19	Front Impact	64	SDSPLUS26.64	Self-Tapping Screw 4.8 x 60-F
20	SDSPLUS26.20	O-Ring 18 x 3.05	65	SDSPLUS26.65	Carbon Brush Cover
21	SDSPLUS26.21	Spring Washer	66	SDSPLUS26.66	Carbon Brush Holder
22	SDSPLUS26.22	Front Impact Spring	67	SDSPLUS26.67	Carbon Brush
23	SDSPLUS26.23	Gear (Large)	68	SDSPLUS26.68	Screw for Button
24	SDSPLUS26.24	Piston Pin	69	SWM4.SB	Spring Washer M4 Black
25	SDSPLUS26.25	Piston	70	FWM4.SB	Flat Washer M4 Black
26	SDSPLUS26.26	Shaft for Piston	71	SDSPLUS26.71	Switch Button
27	SDSPLUS26.27	Oil Bearing	72	SDSPLUS26.72	Spring
28	SDSPLUS26.28	Oil Seal Cover	73	SDSPLUS26.73	Spring Holder
29	SDSPLUS26.29	Work Spindle	74	SDSPLUS26.74	Self-Tapping Screw 4 x 9.5-F
30	SDSPLUS26.30	Gearbox	75	SDSPLUS26.75	Switch Button Base
31	SDSPLUS26.31	Gearbox Seal	76	SDSPLUS26.76	Switch Button Base Support
32	B/6003ZZ	Bearing 6003zz	77	SDSPLUS26.77	Handle, Left Side
33	SDSPLUS26.33	Ext Circlip 35mm	78	SDSPLUS26.78	Capacitor 0.22uF
34	SDSPLUS26.34	Gear 1st	79	SDSPLUS26.79	Switch
35	B/HK1210	Needle Bearing HK1210	80	SDSPLUS26.80	Cable Sleeve
36	SDSPLUS26.36	Support Sleeve	82	SDSPLUS26.82	Cable Grip
37	SDSPLUS26.37	Top Hammer Spring	83	SDSPLUS26.83	Self-Tapping Screw 4 x 16-F
38	SDSPLUS26.38	Round Pin	84	SDSPLUS26.84	Handle, Right Side
39	SDSPLUS26.39	Top Hammer	85	SDSPLUS26.85	Self-Tapping Screw 4 x 45-F
40	SDSPLUS26.40	Gear (Small)	100	SDSPLUS26.S-100	Auxiliary Handle Clamp Ring
41	B/16002ZZ	Bearing 16002Z	101	SDSPLUS26.S-101	T-Bolt for Auxiliary Handle
42	SDSPLUS26.42	Gear Washer (Small)	102	SDSPLUS26.S-102	Auxiliary Side Handle Bracket
43	SDSPLUS26.43	Gear 2nd	103	SDSPLUS26.S-103	Auxiliary Side Handle
44	SB-5.0	Steel Ball 5.0mm	104	SDSPLUS26.S-104	Depth Gauge Ruler Button
45	SDSPLUS26.45	Safety Clutch Plate (A)	105	SDSPLUS26.S-105	Depth Gauge Ruler

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. There may be alternative versions of this product, please contact us should you require this information.

IMPORTANT: No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

01284 703534

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 757500 sales@sealey.co.uk

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR

SDSPLUS26 Issue 1 23/09/19