

CA 1730

Laser distance meter




Accurate, simple and fast!

- Distance measurement up to 60 metres
- Surface / Volume / Addition / Subtraction
Height calculation and continuous measurement mode
- Backlit 4-line display
- Memory with log of the last 20 measurements
- Ruler for remote measurements

Measure up





All the spatial measurements you need, simply and accurately

For construction work, renovation, indoor or outdoor fittings, etc., in the residential and tertiary sectors, the CA 1730 can be used to perform all your distance measurements up to 60 m. This compact instrument fits in one hand and is easy to operate. Its backlit display is particularly easy to read whatever the lighting conditions.

Users have access to area or volume measurements and multiple other functions: addition, subtraction, data storage, etc.



STANDARD STATE AT DELIVERY:

Instrument delivered in a cardboard box with a bag, 2 x AAA batteries, User's Manual in 5 languages and verification certificate.

FOR ORDER:

CA 1730 Distance Meter..... **P01651730**

CA 1730 Distance Meter	
Measurement range	0.2 ~ 60 metres
Accuracy	± 2 mm + 5 x 10 ⁻⁵ Distance
Area & volume measurement	Yes
Addition/Subtraction	Yes
One-shot measurement	Yes
Continuous measurement	Yes
Display	On 4 lines with backlighting
Audible signal	Yes
Data storage	Log of last 20 measurements
Units	m / in / ft / ft+in
Power supply	
Type	Type AAA 2 x 1.5 V
Battery life	Approximately 5,000 measurements
Auto power-off	LASER auto power-off (30 seconds) Instrument auto power-off (180 seconds)
Physical specifications	
Dimensions / Weight	115 x 52 x 32 mm / 118 g
Protection	IP54
Operating range	Temperature: 0 to +40 °C without condensation Storage: -10°C to +60°C
Compliance	Compliance with the IEC/EN 61326-1 or BS EN 61326-1 and IEC/EN 61010-1 and BS EN 61010-1 standards LASER safety standards: IEC 60825-1 LASER: Class II LASER wavelength: 630 nm ~ 670 nm - Power < 1 mW
Warranty	2 years

FRANCE
Chauvin Arnoux
 12 - 16 rue Sarah Bernhardt
 92600 Asnières-sur-Seine
 Tél : +33 1 44 85 44 85
 Fax : +33 1 46 27 73 89
 info@chauvin-arnoux.fr
 www.chauvin-arnoux.fr/com

UNITED KINGDOM
Chauvin Arnoux Ltd
 Unit 1 Nelson Ct, Flagship Sq, Shaw Cross Business Pk
 Dewsbury, West Yorkshire - WF12 7TH
 Tel: +44 1924 460 494
 Fax: +44 1924 455 328
 info@chauvin-arnoux.co.uk
 www.chauvin-arnoux.com

MIDDLE EAST
Chauvin Arnoux Middle East
 P.O. BOX 60-154
 1241 2020 JAL EL DIB - LEBANON
 Tel: +961 1 890 425
 Fax: +961 1 890 424
 camie@chauvin-arnoux.com
 www.chauvin-arnoux.com

CHAUVIN
ARNOUX
 GROUP