

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190160098

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Krimptite Quick Disconnect, Female, for 24-26 (0.20-0.12mm²) Wire, Box, Tab 4.75 x 0.51mm

Documents:

[3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[3D Model](#)

[Product Specification PS-19902-011-001 \(PDF\)](#)

[Product Specification PS-19902-013-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Comments

Crimp Quality Equipment

Insulated

Overview

Product Name

Taxonomy

Type

UPC

Quick Disconnects

19016

Butted Seam

Yes

No

Standard Quick-Disconnect Terminals

Krimptite

Quick Disconnects

Quick Disconnect

800755047585

Physical

Barrel Type

Gender

Glow-Wire Capable

Insulation

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Orientation

Packaging Type

Polarized to Mating Part

Tab Thickness

Tab Width

Temperature Range - Operating

Wire Size AWG

Closed

Female

No

None

None

Brass

Tin

Tin

0.378/g

Straight

Bag

No

0.51mm

4.75mm

Per Wire Specification

24, 26

Electrical

Voltage - Maximum

Per Wire Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

M-1136

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-013-001

SD-19016-004-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/88/2018 (15

January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19016 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool

640030400

Crimp Head for the

640070400

AT-200 Pneumatic

Hand Tool

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION