

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334721301](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: MX150 Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, Keying Option A, without Connector Position Assurance, with Clip-Slot, Black

Documents:

3D Model (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
3D Model	Application Specification AS-33611-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31300-903-001 (PDF)
Product Specification PS-33472-000-001 (PDF)	Datasheet (PDF)
Application Specification AS-33472-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	822348087198

Physical

Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	15.659/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33611-001-001
Packaging Specification	PK-31300-903-001
Product Specification	PS-33472-000-001
Sales Drawing	334721202-001, SD-33472-0001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[33472 Series](#)

Mates With

MX150 Male Sealed Connector [33482](#)

MX150 Male Bulkhead Twist-Lock
Sealed Connector [348406410](#)

Use With

MX150 Female Terminal [33012](#) , [33001](#)

MX150 Sealed Cavity Plug [343450001](#)

MX150 Backshell [349511210](#) ,
[349501220](#)