

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0436450500](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: [Micro-Fit 3.0 Receptacle Housing, Single Row, 5 Circuits, UL 94V-0, Black](#)

Documents:

Drawing (PDF)	Packaging Specification PK-43645-001-001 (PDF)
3D Model (PDF)	Test Summary 430450005-TS-000 (PDF)
3D Model	Test Summary TS-43045-001-001 (PDF)
Product Specification 436500001-PS-JA-000 (PDF)	Test Summary TS-43045-002-001 (PDF)
Product Specification 436500001-PS-KO-000 (PDF)	Test Summary TS-46235-001-001 (PDF)
Product Specification 436500001-PS-SP-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-43650-001 (PDF)	Product Literature (PDF)
Application Specification 430250000-AS-000 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	43645
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Micro-Fit Connector System
Product Name	Micro-Fit 3.0
UPC	800754366205

Physical

Circuits (maximum)	5
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	0.664/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	430250000-AS-000
Packaging Specification	PK-43645-001-001
Product Specification	436500001-PS-JA-000, 436500001-PS-KO-000, 436500001-PS-SP-000, PS-43650-001
Sales Drawing	436450000-SD-000
Test Summary	430450005-TS-000, TS-43045-001-001, TS-43045-002-001, TS-46235-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[43645](#) Series

Mates With

Micro-Fit 3.0 Plug Housings [43640](#)

Micro-Fit TPA Plug Housing [200875](#)

Micro-Fit 3.0 Headers [43650](#)

Micro-Fit 3.0 Cable Assembly [214752](#) ,
[214753](#)

Use With

Micro-Fit 3.0 Female Crimp Terminals
[43030](#)
 Micro-Fit RMF Female Crimp
Terminals [46235](#)
Micro-Fit 3.0 Pre-
Crimped Leads [797580002](#) , [797580004](#) ,
[797580010](#) , [797580012](#) , [214760](#) , [214761](#)

This document was generated on 08/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION