

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0050842032](#)
Status: **Active**
Overview: [MLX Power Connectors](#)
Description: 2.13mm Diameter MLX Pin and Socket Receptacle, 3 Circuits, Natural

Documents:

Drawing (PDF)	Packaging Specification PK-42022-XX-001 (PDF)
3D Model	Test Summary TS-42022-0001-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-42022-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	42022
Application	Power, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number 366440003 . Current – Maximum per contact 20A if used with 36663 and 36664 terminal

Overview

Product Name	MLX Power Connectors
UPC	MLX 800754386470

Physical

Circuits (maximum)	3
Circuits Detail	3
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.230/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	Yes
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C

Electrical

Current - Maximum per Contact	20.0A
-------------------------------	-------

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	42022-3C
--------------------	----------

Reference - Drawing Numbers

Packaging Specification	PK-42022-XX-001
Product Specification	PS-42022-0001-001
Sales Drawing	SD-42022-XX-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42022 Series](#)

Mates With

MLX Power Crimp Housing Plug [42021](#)

Use With

MLX Crimp Terminal [42023](#) , [42024](#) . MLX Male Pre-Crimped Lead [797582029](#) , [797582030](#) . MLX Female Pre-Crimped Lead [797582031](#) , [797582032](#)

This document was generated on 08/16/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION