

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0469920410

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Jr. Receptacle Housing, Dual Row, Nylon 6/6, UL 94V-2, 4 Circuits, Glow-Wire Capable, Black

Documents:	
3D Model (PDF)	Packaging Specification PK-5557-002-000 (PDF)
3D Model	Test Summary 457500003-TS-000 (PDF)
Drawing (PDF)	Test Summary 55560010-TS-000 (PDF)
Product Specification PS-45750-001-001 (PDF)	Test Summary 55570003-TS-000 (PDF)
Product Specification PS-5556-001-001 (PDF)	Test Summary TS-5556-002-001 (PDF)
Application Specification 55560001-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	46992
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Jr.
UPC	887191637372

Physical

Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.147/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	55560001-AS-000
Packaging Specification	PK-5557-002-000
Product Specification	PS-45750-001-001, PS-5556-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[46992](#) Series

Mates With

Mini-Fit Jr. Plug [46993](#) . Mini-Fit Jr. Reflow
Solder Capable Header [46991](#)

Use With

Mini-Fit Female Crimp Terminal [5556](#) . Mini-
Fit Plus HCS Crimp Terminal [45750](#)

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION