


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0050842030](#)  
**Status:** **Active**  
**Overview:** [MLX Power Connectors](#)  
**Description:** 2.13mm Diameter MLX Pin and Socket Receptacle, 3 Circuits, Natural

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification PK-42022-XX-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Test Summary TS-42022-0001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-42022-0001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">42022</a>
Application	Power, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number <a href="#">366440003</a> . Current – Maximum per contact 20A if used with <a href="#">36663</a> and <a href="#">36664</a> terminal

Overview

Product Name	<a href="#">MLX Power Connectors</a>
UPC	MLX 800753577428

**Physical**

Circuits (maximum)	3
Circuits Detail	3
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.120/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	Yes
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C

**Electrical**

Current - Maximum per Contact	20.0A
-------------------------------	-------

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	42022-3A
--------------------	----------

**Reference - Drawing Numbers**

Packaging Specification	PK-42022-XX-001
Product Specification	PS-42022-0001-001
Sales Drawing	SD-42022-XX-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[42022 Series](#)

**Mates With**

MLX Power Crimp Housing Plug [42021](#)

**Use With**

MLX Crimp Terminal [42023](#) , [42024](#) . MLX Male Pre-Crimped Lead [797582029](#) , [797582030](#) . MLX Female Pre-Crimped Lead [797582031](#) , [797582032](#)

This document was generated on 08/18/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**