

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0747370009](#)
Status: **Active**
Overview: [SFP+ and SFP Interconnect Solutions](#)
Description: [SFP One Piece Cage, EMI Shielding, 3.05mm Press-Fit Tails](#)

Documents:
[3D Model](#) [Product Specification PS-74737-8001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Application Specification AS-74737-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-74737-0010-001 \(PDF\)](#)

Application tooling part link
[Application Tooling Part Link](#) 62202-9745
[Application Tooling Part Link](#) 62202-9750


General
Product Family [EMI Cages](#)
Series [74737](#)
Application [Module-to-Board](#)
Component Type [Cage Assembly](#)
Overview [SFP+ and SFP Interconnect Solutions](#)
Product Name [SFP](#)
UPC [822350185813](#)

Physical
EMI Panel / Bezel Mount [Spring Fingers](#)
Light Pipes per Port [0](#)
Material - Metal [Copper Alloy](#)
Net Weight [4.309/g](#)
Orientation [Horizontal](#)
Packaging Type [Tray](#)
Port Configuration [1x1](#)
Rear Legs [3](#)
Termination Interface: Style [Through Hole - Compliant Pin](#)
Thermal Height [N/A](#)
Thermal Solutions [Closed Top](#)

Solder Process Data
Lead-freeProcess Capability [SMC&WAVE](#)
Process Temperature max. C [265](#)

Material Info
Engineering Number [73927-0009](#)

Reference - Drawing Numbers
[Application Specification](#) [AS-74737-001-001](#)
[Product Specification](#) [PS-74737-0010-001, PS-74737-8001-001](#)
[Sales Drawing](#) [747370009-ASY, SD-74737-0009-001,](#)
[SD-74737-009-001, SD-74737-020-001](#)



Series image - Reference only

EU ELV
Compliant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Compliant
RoHS Phthalates Not Contained

Search Parts in this Series
[74737 Series](#)

Mates With
[74720](#) SFP Copper Module, [73929](#) SFP
Cable Assembly, Passive, 2 Gbps, [73930](#)
SFP Cable Assembly, Active, 2 Gbps, [74742](#)
SFP Cable Assembly, Passive, 4 Gbps,
[74743](#) SFP Cable Assembly, Active, 4 Gbps

Use With
[74441](#) Connector