

Housing set - UM-BASIC-KIT-B108-L60-7035 - 1300352


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Profile housing (PVC), mounting type: DIN rail mounting, color: light gray (7035), dimensions on the DIN rail: width: 63.8 mm, height: 127.8 mm, depth: 39.45 mm, incl. 2 lateral elements (PA), color: light gray (7035), for PCBs with width: 108 mm, length: 60 mm, PCB surface: 4510 mm²



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 544577
GTIN	4063151544577
Custom tariff number	39169010

Technical data

Product properties

Brief article description	Housing set
Type	UM-BASIC-KIT-B108-L60-7035
Item no.	1300352
Housing type	Profile housing
Housing series	UM-BASIC
Type	incl. 2 lateral elements
Mounting type	DIN rail mounting

Dimensions

Width	63.8 mm
Height	127.8 mm
Depth	39.45 mm
Depth from top edge of DIN rail	32.45 mm

PCB specifications

Number of PCB holders	3
Dimensions	108 mm x 60 mm (PCB dimensions)

Housing set - UM-BASIC-KIT-B108-L60-7035 - 1300352

Technical data

PCB specifications

PCB surface, maximum	4510 mm ²
PCB thickness	1.4 mm ... 1.8 mm
Mounting position	parallel to the DIN rail
Type of PCB mount	Insertion/securing with additional elements

Material specifications - Profile

Material	PVC
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

Material specifications - Lateral elements

Material	PA
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 50 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Ambient temperature (operation)	-15 °C ... 50 °C (depending on power dissipation)
Relative humidity (storage/transport)	95 %

General information

Type of note	Assembly instruction:
Note	Please observe the assembly instructions available in the download area.

Packaging specifications

Type of packaging	packed in cardboard
Pieces per package	1
Denomination packing units	Pcs.
Outer packaging type	Carton

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 11.0	27182701
eCl@ss 9.0	27182701

Approvals

Approvals

Housing set - UM-BASIC-KIT-B108-L60-7035 - 1300352

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868
