

# Housing set - UM-BASIC-KIT-B108-L150-7035 - 1300356

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Profile housing (PVC), mounting type: DIN rail mounting, color: light gray (7035), dimensions on the DIN rail: width: 153.8 mm, height: 127.8 mm, depth: 39.45 mm, incl. 2 lateral elements (PA), color: light gray (7035), for PCBs with width: 108 mm, length: 150 mm, PCB surface: 13780 mm²



# **Key Commercial Data**

Packing unit	1 pc
GTIN	4 063151 544744
GTIN	4063151544744
Custom tariff number	39169010

#### Technical data

#### Product properties

Brief article description	Housing set
Туре	UM-BASIC-KIT-B108-L150-7035
Item no.	1300356
Housing type	Profile housing
Housing series	UM-BASIC
Туре	incl. 2 lateral elements
Mounting type	DIN rail mounting

#### **Dimensions**

Width	153.8 mm
Height	127.8 mm
Depth	39.45 mm
Depth from top edge of DIN rail	32.45 mm

#### PCB specifications

Number of PCB holders	3
Dimensions	108 mm x 150 mm (PCB dimensions)



# Housing set - UM-BASIC-KIT-B108-L150-7035 - 1300356

# Technical data

# PCB specifications

PCB surface, maximum	13780 mm²
PCB thickness	1.4 mm 1.8 mm
Mounting position	parallel to the DIN rail
Type of PCB mount	Insertion/securing with additional elements

# Material specifications - Profile

Material	PVC
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

#### Material specifications - Lateral elements

Material	PA
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

#### Ambient conditions

Ambient temperature (storage/transport)	-40 °C 50 °C
Ambient temperature (assembly)	-5 °C 50 °C
Ambient temperature (operation)	-15 °C 50 °C (depending on power dissipation)
Relative humidity (storage/transport)	95 %

# General information

Type of note	Assembly instruction:
I Note	Please observe the assembly instructions available in the download area.

# Packaging specifications

Type of packaging	packed in cardboard
Pieces per package	1
Denomination packing units	Pcs.
Outer packaging type	Carton

# Classifications

#### eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 11.0	27182701
eCl@ss 9.0	27182701

# Approvals

# Approvals



# Housing set - UM-BASIC-KIT-B108-L150-7035 - 1300356

Approvals		
Approvals		
UL Recognized		
Ex Approvals		
Approval details		
UL Recognized	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868

Phoenix Contact 2021 © - all rights reserved http://www.phoenixcontact.com