

# QPD STAS 3PE1,5 BK - Connector



1490382

<https://www.phoenixcontact.com/de/produkte/1490382>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, product family: QPD, connection method: IDC connection, number of positions: 3+PE, 0.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, 400 V, 16 A AC, black, with one QUICKON nut, external cable diameter: 7 mm ... 13 mm, Connectors for the motor connection of Venetian blinds, blinds, roller shutters, and awnings

## Your advantages

- Compatible with all classic motor connections for Venetian blinds, blinds, roller shutters, and awnings
- Convenient: quick and easy assembly without special tools
- Innovative and time saving - QUICKON fast connection for time saving of up to 80 % for on-site connection
- Safer connection with mechanical coding to protect against mismatching, and touch-proof protection in accordance with DIN EN 0105

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1490382             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Sales key                            | D1 - Steckverbinder |
| Product key                          | BF6BBA              |
| GTIN                                 | 4063151936839       |
| Weight per piece (including packing) | 42,166 g            |
| Weight per piece (excluding packing) | 42,166 g            |
| Customs tariff number                | 85366990            |
| Country of origin                    | PL                  |

# QPD STAS 3PE1,5 BK - Connector



1490382

<https://www.phoenixcontact.com/de/produkte/1490382>

## Technical data

### Notes

|                     |                                                                                          |
|---------------------|------------------------------------------------------------------------------------------|
| Assembly note       | <b>NOTE:</b> Tighten the QUICKON nut all the way to the stop or to the specified torque. |
| Notes on connection | You will find notes on assembly in our assembly video.                                   |

### Product properties

|                                    |                        |
|------------------------------------|------------------------|
| Product type                       | Installation connector |
| Product family                     | QPD                    |
| Number of positions                | 4                      |
| Connection profile                 | 3+PE                   |
| Position marking                   | 1, 2, 3, PE            |
| Number of connections per position | 1                      |

### Data management status

|                  |    |
|------------------|----|
| Article revision | 01 |
|------------------|----|

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                             |          |
|-----------------------------|----------|
| Rated surge voltage (III/3) | 6 kV     |
| Rated voltage (III/3)       | 400 V    |
| Nominal voltage $U_N$       | 400 V AC |
|                             | 250 V DC |
| Nominal current $I_N$       | 16 A AC  |
|                             | 10 A DC  |

### Connection data

#### Connection technology

|                                                                       |                |
|-----------------------------------------------------------------------|----------------|
| Connection method On the device side                                  | IDC connection |
| Frequency of connections between conductors of the same cross section | max. 10        |

#### Conductor connection

|                                  |                                             |
|----------------------------------|---------------------------------------------|
| Conductor cross section flexibel | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross section solid    | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Connection cross section AWG     | 20 ... 16                                   |
| Tightening torque Union nut      | 8 Nm                                        |


### Dimensions

# QPD STAS 3PE1,5 BK - Connector

1490382

<https://www.phoenixcontact.com/de/produkte/1490382>



|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 27.5 mm                                                                            |
| Height              | 26 mm                                                                              |
| Length              | 66 mm                                                                              |

## Material specifications

|                          |                   |
|--------------------------|-------------------|
| Color                    | black (RAL 9005)  |
| Material wire insulation | PVC/PE/TPE/rubber |
| Contact material         | CuZn              |
| Contact surface material | silver-plated     |
| Contact carrier material | PA                |

## Cable/line

|                                                                             |                                           |
|-----------------------------------------------------------------------------|-------------------------------------------|
| Structure of individual litz in acc. with VDE 0295 / smallest wire diameter | VDE 0295 class 1 to 6/min. 0.15 mm        |
| External cable diameter                                                     | 7 mm ... 13 mm                            |
| Wire diameter including insulation                                          | 1.6 mm ... 3 mm                           |
| Position marking                                                            | 1, 2, 3, PE                               |
| Single wire, color                                                          | Blue 1, black 2, brown 3, green-yellow PE |

## Mechanical properties

|                             |    |
|-----------------------------|----|
| Mechanical data             |    |
| Insertion/withdrawal cycles | 50 |

## Environmental and real-life conditions

|                                         |                   |
|-----------------------------------------|-------------------|
| Ambient conditions                      |                   |
| Degree of protection                    | IP54              |
| Ambient temperature (operation)         | -40 °C ... 100 °C |
| Temperature when conductor connected    | -5 °C ... 50 °C   |
| Ambient temperature (storage/transport) | -40 °C ... 100 °C |

# QPD STAS 3PE1,5 BK - Connector


1490382

<https://www.phoenixcontact.com/de/produkte/1490382>



## Drawings

Dimensional drawing



Length = 66 mm, with QUICKON nut screwed to the stop

# QPD STAS 3PE1,5 BK - Connector

1490382

<https://www.phoenixcontact.com/de/produkte/1490382>



## Approvals

💡 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/de/produkte/1490382>



**VDE Zeichengenehmigung**

Approval ID: 40051487

# QPD STAS 3PE1,5 BK - Connector



1490382

<https://www.phoenixcontact.com/de/produkte/1490382>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27440605 |
| ECLASS-12.0 | 27440605 |
| ECLASS-13.0 | 27440605 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002560 |
|----------|----------|

# QPD STAS 3PE1,5 BK - Connector



1490382

<https://www.phoenixcontact.com/de/produkte/1490382>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

# QPD STAS 3PE1,5 BK - Connector



1490382

<https://www.phoenixcontact.com/de/produkte/1490382>

## Mandatory accessories

### QPD STAK 3PE1,5 BK - Connector

1065121

<https://www.phoenixcontact.com/de/produkte/1065121>



Connector, product family: QPD, connection method: IDC connection, number of positions: 3+PE, 0.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, 400 V, 16 A AC, black, with one QUICKON nut, external cable diameter: 7 mm ... 13 mm, Connectors for the motor connection of Venetian blinds, blinds, roller shutters, and awnings

---

## Accessories

### SEALING PLUG 10X16 RD - Closing cap

1400284

<https://www.phoenixcontact.com/de/produkte/1400284>



Closing cap, for threads pluggable, color: red

# QPD STAS 3PE1,5 BK - Connector

1490382

<https://www.phoenixcontact.com/de/produkte/1490382>



## UNIFOX-WRENCH - Screw pliers

1212835

<https://www.phoenixcontact.com/de/produkte/1212835>



Screw pliers, with fast adjustment, for wrench size 10 mm ... 36 mm, size: 260 mm

---

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH

Flachsmarktstraße 8

D-32825 Blomberg

+49 52 35/3-1 20 00

[info@phoenixcontact.de](mailto:info@phoenixcontact.de)