




essential POWER CORDS

CORD SET
INTERCONNECTION CORD SET
powerCON® FXX



**TRUST
THE
ORIGINAL**

NEUTRIK®

A brand of the Neutrik Group

essential POWER CORDS



*Experience full compliance, unwavering reliability,
and top-notch safety, all within your budget.*



- ★ HIGHLY RELIABLE
- ★ FULLY COMPLIANT
- ★ MADE IN EUROPE
- ★ BEST PRICE



QUALITY, RELIABILITY AND SAFETY

COMPLIANCE MATTERS

The new NEUTRIK powerCON FXX series connectors proudly carry the IEC-EN 60320-1 certification, complying with all required norms and standards. You can trust that your equipment is in good hands with NEUTRIK.

SAFETY FIRST

At NEUTRIK, we prioritize your safety above all else. Our cables are rigorously tested and certified to ensure they meet the highest safety standards in the industry.

EXPERIENCE RELIABILITY

These cords guarantee the top-tier reliability. Embrace confidence with our cutting-edge ruggedized powerCON FXX connectors paired with high-quality cables.

EUROPEAN CRAFTSMANSHIP

Our cables are proudly produced in Europe, adhering to the highest manufacturing standards. European production guarantees precision, quality, and reliability that you can count on

BEST PRICE

We prioritize high quality, unmatched safety standards, and cost efficiency! With our in-house connectors manufacturing and state-of-the-art, cost-effective power cord production site, we bring you affordable prices that redefine value for money.



**TRUST
THE
ORIGINAL**

essential powerCON® FXX POWER CORDS

INTERCONNECTION CORD SET (NKPH01/02/11-A4A3-*)



EN IEC 60799

EN IEC 60320-1

BREAKING CAPACITY

H07RN-F


H05VV-F

3 x 2,5mm²

3 x 1,5mm²

IP20

CORD SET (NKPH01/02-MFA3-*)



EN IEC 60799

EN IEC 60320-1

BREAKING CAPACITY

ANTI KINK PROTECTION


H07RN-F

3 x 2,5mm²

3 x 1,5mm²

IP20

CORD SET (NKPH11-MFA3-*)



EN IEC 60799

EN IEC 60320-1

BREAKING CAPACITY

H05VV-F

3 x 1,5mm²

IP20

REWIRABLE CORDS

INTERCONNECTION CORD SETS

Order No.	Product name	Connector 1	Connector 2	Cable type	Conductor	Length
1036398	NKPH01-A4A3-M0100	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G1.5	1,5 mm ²	1 m
1036399	NKPH01-A4A3-M0150	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G1.5	1,5 mm ²	1,5 m
1036400	NKPH01-A4A3-M0200	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G1.5	1,5 mm ²	2 m
1036401	NKPH01-A4A3-M0300	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G1.5	1,5 mm ²	3 m
1036402	NKPH01-A4A3-M0500	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G1.5	1,5 mm ²	5 m
1036403	NKPH01-A4A3-M1000	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G1.5	1,5 mm ²	10 m
1036404	NKPH02-A4A3-M0100	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G2.5	2,5 mm ²	1 m
1036405	NKPH02-A4A3-M0150	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G2.5	2,5 mm ²	1,5 m
1036406	NKPH02-A4A3-M0200	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G2.5	2,5 mm ²	2 m
1036407	NKPH02-A4A3-M0300	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G2.5	2,5 mm ²	3 m
1036408	NKPH02-A4A3-M0500	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G2.5	2,5 mm ²	5 m
1036409	NKPH02-A4A3-M1000	powerCON NAC3FXXB	powerCON NAC3FXXA	H07RN-F3G2.5	2,5 mm ²	10 m
1036414	NKPH11-A4A3-M0100	powerCON NAC3FXXB	powerCON NAC3FXXA	H05VV-F3G1.5	1,5 mm ²	1 m
1036415	NKPH11-A4A3-M0150	powerCON NAC3FXXB	powerCON NAC3FXXA	H05VV-F3G1.5	1,5 mm ²	1,5 m
1036416	NKPH11-A4A3-M0200	powerCON NAC3FXXB	powerCON NAC3FXXA	H05VV-F3G1.5	1,5 mm ²	2 m
1036417	NKPH11-A4A3-M0300	powerCON NAC3FXXB	powerCON NAC3FXXA	H05VV-F3G1.5	1,5 mm ²	3 m
1036418	NKPH11-A4A3-M0500	powerCON NAC3FXXB	powerCON NAC3FXXA	H05VV-F3G1.5	1,5 mm ²	5 m
1036419	NKPH11-A4A3-M1000	powerCON NAC3FXXB	powerCON NAC3FXXA	H05VV-F3G1.5	1,5 mm ²	10 m

REWIRABLE CORDS

CORD SETS

Order No.	Product name	Connector 1	Connector 2	Cable type	Conductor	Length
1036410	NKPH01-MFA3-M0150	Schuko E+F anti-kink	powerCON NAC3FXXA	H07RN-F3G1.5	1,5 mm ²	1,5 m
1036411	NKPH01-MFA3-M0300	Schuko E+F anti-kink	powerCON NAC3FXXA	H07RN-F3G1.5	1,5 mm ²	3 m
1036412	NKPH02-MFA3-M0150	Schuko E+F anti-kink	powerCON NAC3FXXA	H07RN-F3G2.5	2,5 mm ²	1,5 m
1036413	NKPH02-MFA3-M0300	Schuko E+F anti-kink	powerCON NAC3FXXA	H07RN-F3G2.5	2,5 mm ²	3 m
1036420	NKPH11-MFA3-M0150	Schuko E+F	powerCON NAC3FXXA	H05VV-F3G1.5	1,5 mm ²	1,5 m
1036421	NKPH11-MFA3-M0300	Schuko E+F	powerCON NAC3FXXA	H05VV-F3G1.5	1,5 mm ²	3 m

ACCESSORIES

FOR CABLE CONNECTOR



SCNAC-FX

SCNAC-FX	Rubber cover (female)
----------	-----------------------

essential

FEATURES AND BENEFITS



Dismountable with special tools only
(acc. EN IEC60320)


**Durable high-quality
rubber jacketed cables**




Rugged and durable design

Circuit Breaking Capacity (CBC) Connector
(acc. EN IEC60320)

- powerCON FXX Series connector with CBC (Circuit Breaking Capacity)
- Fully norm compliant acc. EN IEC 60799 / EN IEC 60320-1
- High quality H07RN-F and H05VV-F cables with conductor cross section of 1.5mm² and 2.5mm²
- Highly reliable and cost effective
- Manufactured in Europe






LIECHTENSTEIN (HEADQUARTERS)

Neutrik AG, Im alten Riet 143,

9494 Schaan, Liechtenstein

T +423 237 24 24, F +423 232 53 93, neutrik@neutrikgroup.com



Power cords essential series Folder – NF36 – 2023 12 – Data subject to change without prior notice. © 2023 NEUTRIK®.
NEUTRIK®, powerCON® are registered trademarks of Neutrik AG. ALL RIGHTS RESERVED.

www.neutrik.com

NEUTRIK®

A brand of the Neutrik Group