

Ring terminals 4.3 ... 10.5 mm (M4 - M10) for cables \varnothing 0.5 ... 6 mm² 100 pcs set



RoHS



Quadrios insulated ring terminals guarantee optimal electrical and mechanical connections in conjunction with fitting crimping tools. This product series includes a variation of most used colors and sizes, perfect for daily use. The ring terminals are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. Optimal for use with suitable ring terminal crimping pliers.

Technical data: Voltage (max.): 600 V, Material: Vinyl PVC (insulation) / Material: copper (tin plated) • Hole- \varnothing : 4.3 ... 10.5 mm • Thread size: M4 ... M10 • Cross-section: 0.5 ... 6 mm² • Color: red, blue, black, yellow • Content: 100 pcs pack.

Part No.	Description	Cross-section	Hole diameter	Thread size	Color	EAN / GTIN	Content
22C441	Ring terminals red, hole-dia. 4.3 mm	0.5 - 1.5 mm ²	4.3 mm	M4	Red	4260732281016	100 pcs
22C442	Ring terminals red, hole-dia. 5.3 mm	0.5 - 1.5 mm ²	5.3 mm	M5	Red	4260732281023	100 pcs
22C443	Ring terminals red, hole-dia. 6.5 mm	0.5 - 1.5 mm ²	6.5 mm	M6	Red	4260732281030	100 pcs
22C444	Ring terminals red, hole-dia. 8.5 mm	0.5 - 1.5 mm ²	8.5 mm	M8	Red	4260732281047	100 pcs
22C445	Ring terminals red, hole-dia. 10.5 mm	0.5 - 1.5 mm ²	10.5 mm	M10	Red	4260732281054	100 pcs
22C446	Ring terminals blue, hole-dia. 4.3 mm	1.5 - 2.5 mm ²	4.3 mm	M4	Blue	4260732281061	100 pcs
22C447	Ring terminals blue, hole-dia. 5.3 mm	1.5 - 2.5 mm ²	5.3 mm	M5	Blue	4260732281078	100 pcs
22C448	Ring terminals blue, hole-dia. 6.5 mm	1.5 - 2.5 mm ²	6.5 mm	M6	Blue	4260732281085	100 pcs
22C449	Ring terminals blue, hole-dia. 8.5 mm	1.5 - 2.5 mm ²	8.5 mm	M8	Blue	4260732281092	100 pcs
22C450	Ring terminals blue, hole-dia. 10.5 mm	1.5 - 2.5 mm ²	10.5 mm	M10	Blue	4260732281108	100 pcs
22C451	Ring terminals black, hole-dia. 4.3 mm	2.5 - 4 mm ²	4.3 mm	M4	Black	4260732281115	100 pcs
22C452	Ring terminals black, hole-dia. 5.3 mm	2.5 - 4 mm ²	5.3 mm	M5	Black	4260732281122	100 pcs
22C453	Ring terminals black, hole-dia. 6.5 mm	2.5 - 4 mm ²	6.5 mm	M6	Black	4260732281139	100 pcs
22C454	Ring terminals black, hole-dia. 8.5 mm	2.5 - 4 mm ²	8.5 mm	M8	Black	4260732281146	100 pcs
22C455	Ring terminals black, hole-dia. 10.5 mm	2.5 - 4 mm ²	10.5 mm	M10	Black	4260732281153	100 pcs
22C456	Ring terminals yellow, hole-dia. 4.3 mm	4 - 6 mm ²	4.3 mm	M4	Yellow	4260732281160	100 pcs
22C457	Ring terminals yellow, hole-dia. 5.3 mm	4 - 6 mm ²	5.3 mm	M5	Yellow	4260732281177	100 pcs
22C458	Ring terminals yellow, hole-dia. 6.5 mm	4 - 6 mm ²	6.5 mm	M6	Yellow	4260732281184	100 pcs
22C459	Ring terminals yellow, hole-dia. 8.5 mm	4 - 6 mm ²	8.5 mm	M8	Yellow	4260732281191	100 pcs
22C460	Ring terminals yellow, hole-dia. 10.5 mm	4 - 6 mm ²	10.5 mm	M10	Yellow	4260732281207	100 pcs

Connection only by qualified electricians!