



Round-Plug Bullet Connector (M/F)

Ø 4 mm & 5 mm / 0.5...6 mm²

100 pcs set



Round-Plug Bullet Connector Male



Round-Plug Bullet Connector Female

Quadrios round plug connector guarantee optimal electrical and mechanical connections in conjunction with fitting crimping tools. Connection only by qualified electricians! We assume no liability or warranty in case of incorrect application.

Technical data: Material: Brass (plating: tin), PVC (insulation) • Temperature-range: -10°C ... 75°C • Cross-section: 0.5 mm² ... 6 mm² • AWG: 22 ... 10 • Content: 100 parts/set (50x male, 50x female).

Item No.: 23C490 (100 pcs. Set 4 mm, Red)

EAN/GTIN: 4260732283249

Type	Color	Cable size mm ²	Cable size AWG	Diameter (b, Bø)	Dimensions (mm, ± 0.3)	Max. current	Content
Male	Red	0.5 ... 1.5 mm ²	22 ... 16	4 mm	F: 10.5, Dø: 3.5, H: 10.5, L: 21	10 A	50 pcs.
Female	Red	0.5 ... 1.5 mm ²	22 ... 16	4 mm	Bø: 6.3, bø: 4, Dø: 1.7, F: 13, L: 23.5	10 A	50 pcs.

Item No.: 23C491 (100 pcs. Set 4 mm, Blue)

EAN/GTIN: 4260732283256

Type	Color	Cable size mm ²	Cable size AWG	Diameter (b, Bø)	Dimensions (mm, ± 0.3)	Max. current	Content
Male	Blue	1.5 ... 2.5 mm ²	16 ... 14	4 mm	F: 10.5, Dø: 2.3, H: 10.5, L: 21	15 A	50 pcs.
Female	Blue	1.5 ... 2.5 mm ²	16 ... 14	4 mm	Bø: 5.9, bø: 4, Dø: 2.3, F: 13, L: 23.5	15 A	50 pcs.

Item No.: 23C492 (100 pcs. Set 5 mm, Blue)

EAN/GTIN: 4260732283263

Type	Color	Cable size mm ²	Cable size AWG	Diameter (b, Bø)	Dimensions (mm, ± 0.3)	Max. current	Content
Male	Blue	1.5 ... 2.5 mm ²	16 ... 14	5 mm	F: 10.5, Dø: 2.3, H: 10.5, L: 21	15 A	50 pcs.
Female	Blue	1.5 ... 2.5 mm ²	16 ... 14	5 mm	Bø: 6.9, bø: 4.9, Dø: 2.3, F: 13, L: 24	15 A	50 pcs.

Item No.: 23C493 (100 pcs. Set 5 mm, Yellow)

EAN/GTIN: 4260732283270

Type	Color	Cable size mm ²	Cable size AWG	Diameter (b, Bø)	Dimensions (mm, ± 0.3)	Max. current	Content
Male	Yellow	4 ... 6 mm ²	12 ... 10	5 mm	F: 12, Dø: 2.3, H: 13.5, L: 25.5	24 A	50 pcs.
Female	Yellow	4 ... 6 mm ²	12 ... 10	5 mm	Bø: 7.1, bø: 4.9, Dø: 3.5, F: 13, L: 25	24 A	50 pcs.