

## Ring terminals with Shrinking-tube 4.3 ... 10.5 mm (M4 ... M10), for cables $\varnothing$ 0.5 ... 6 mm<sup>2</sup> 50 pcs set



Quadrios ring terminals with shrinking tube guarantee optimal electrical and mechanical connections in conjunction with fitting crimping tools. This product series includes a variation of most used sizes, perfect for daily use. The ring terminals are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. Optimal for use with suitable crimping pliers.

**Technical data:** Voltage (max.): 600 V, Material: copper (tin plated) • Hole diameter: 4.3 ... 10.5 mm • Thread size: M4 ... M10 • Cross-section: 0.5 ... 6 mm<sup>2</sup> • Shrink-ratio: 3:1 • Shrink-Temp.: 90 ... 130 °C • Color: Red, Blue, Yellow • Content: 50 pcs pack.

| Part No. | Description  | Cross-section             | Hole diameter | Thread size | Color  | EAN / GTIN    | Content |
|----------|--|---------------------------|---------------|-------------|--------|---------------|---------|
| 23C516   | Ring terminals Red M4, 0,5 - 1,5 mm <sup>2</sup> $\varnothing$ 4.3 mm    | 0.5 - 1.5 mm <sup>2</sup> | 4.3 mm        | M4          | Red    | 4260732285052 | 50 pcs  |
| 23C517   | Ring terminals Red M5, 0,5 - 1,5 mm <sup>2</sup> $\varnothing$ 5.3 mm    | 0.5 - 1.5 mm <sup>2</sup> | 5.3 mm        | M5          | Red    | 4260732285069 | 50 pcs  |
| 23C518   | Ring terminals Red M6, 0,5 - 1,5 mm <sup>2</sup> $\varnothing$ 6.5 mm    | 0.5 - 1.5 mm <sup>2</sup> | 6.5 mm        | M6          | Red    | 4260732285076 | 50 pcs  |
| 23C519   | Ring terminals Red M8, 0,5 - 1,5 mm <sup>2</sup> $\varnothing$ 8.5 mm    | 0.5 - 1.5 mm <sup>2</sup> | 8.5 mm        | M8          | Red    | 4260732285083 | 50 pcs  |
| 23C520   | Ring terminals Red M10, 0,5 - 1,5 mm <sup>2</sup> $\varnothing$ 10.5 mm  | 0.5 - 1.5 mm <sup>2</sup> | 10.5 mm       | M10         | Red    | 4260732285090 | 50 pcs  |
| 23C521   | Ring terminals Blue M4, 1,5 - 2,5 mm <sup>2</sup> $\varnothing$ 4.3 mm   | 1.5 - 2.5 mm <sup>2</sup> | 4.3 mm        | M4          | Blue   | 4260732285106 | 50 pcs  |
| 23C522   | Ring terminals Blue M5, 1,5 - 2,5 mm <sup>2</sup> $\varnothing$ 5.3 mm   | 1.5 - 2.5 mm <sup>2</sup> | 5.3 mm        | M5          | Blue   | 4260732285113 | 50 pcs  |
| 23C523   | Ring terminals Blue M6, 1,5 - 2,5 mm <sup>2</sup> $\varnothing$ 6.5 mm   | 1.5 - 2.5 mm <sup>2</sup> | 6.5 mm        | M6          | Blue   | 4260732285120 | 50 pcs  |
| 23C524   | Ring terminals Blue M8, 1,5 - 2,5 mm <sup>2</sup> $\varnothing$ 8.5 mm   | 1.5 - 2.5 mm <sup>2</sup> | 8.5 mm        | M8          | Blue   | 4260732285137 | 50 pcs  |
| 23C525   | Ring terminals Blue M10, 1,5 - 2,5 mm <sup>2</sup> $\varnothing$ 10.5 mm | 1.5 - 2.5 mm <sup>2</sup> | 10.5 mm       | M10         | Blue   | 4260732285144 | 50 pcs  |
| 23C526   | Ring terminals Yellow M4, 4 - 6 mm <sup>2</sup> $\varnothing$ 4.3 mm     | 4 - 6 mm <sup>2</sup>     | 4.3 mm        | M4          | Yellow | 4260732285151 | 50 pcs  |
| 23C527   | Ring terminals Yellow M5, 4 - 6 mm <sup>2</sup> $\varnothing$ 5.3 mm     | 4 - 6 mm <sup>2</sup>     | 5.3 mm        | M5          | Yellow | 4260732285168 | 50 pcs  |
| 23C528   | Ring terminals Yellow M6, 4 - 6 mm <sup>2</sup> $\varnothing$ 6.5 mm     | 4 - 6 mm <sup>2</sup>     | 6.5 mm        | M6          | Yellow | 4260732285175 | 50 pcs  |
| 23C529   | Ring terminals Yellow M8, 4 - 6 mm <sup>2</sup> $\varnothing$ 8.5 mm     | 4 - 6 mm <sup>2</sup>     | 8.5 mm        | M8          | Yellow | 4260732285182 | 50 pcs  |
| 23C530   | Ring terminals Yellow M10, 4 - 6 mm <sup>2</sup> $\varnothing$ 10.5 mm   | 4 - 6 mm <sup>2</sup>     | 10.5 mm       | M10         | Yellow | 4260732285199 | 50 pcs  |

Connection only by qualified electricians!