




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Female Screwlock Assembly Kit**

Screw Length: **18.99 mm [.748 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Female Screwlock Assembly Kit

Mechanical Attachment

Screw Plating Material	Zinc
Screwlock Style	Screwlock with Lockwasher and Hex Nut
Screw Material	Cold Rolled Steel
Screw Finish	Yellow Chromate
Screw & Hole Thread Size	4-40
Screw Length	18.99 mm[.748 in]

Dimensions

Thread Length	14.22 mm[.56 in]
---------------	------------------

Operation/Application

For Use With	All Plastic Connectors with Integral Standoffs (HD or HDF)
--------------	--

Packaging Features

Packaging Quantity	1
Packaging Method	Bag, Kit



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5207719-3
KIT SCREWLOCK FEMALE CLEAR ZIN

TE Part # 5207720-2
FEMALE SCREWLOCK,ZN

Also in the Series | AMPLIMITE Kit



D-Sub Backshells & Clamps(136)

D-Sub Contact Accessories(1)

D-Sub Covers(3)

D-Sub Locking & Mounting(122)

Customers Also Bought

TE Part #1658670-2
D-Sub Connector Contacts: Pin, Brass, Signal, Size 22

TE Part #1658686-2
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 22

TE Part #102387-1
10 MODIV HSG COMP DR .100 POL

TE Part #103670-8
09 MTE HDR SRST LATCH W/HLDWN

TE Part #2-1879073-3
Power Resistor: Aluminum Housed, 75 Watt

TE Part #1-84952-4
1MM FPC HORZ.BTTM CONT.ASS.14P

TE Part #1986525-2
Hi Rise Header, 5.0mm, 2 posn

TE Part #1986525-4
Hi Rise Header, 5.0mm, 4 posn

TE Part #1977830-1
DIP SWITCH GDH02SA04

TE Part #YDJT16F13-35PNV001
PLUG ASSY

Documents

Product Drawings
KIT SCREWLOCK FEMALE

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5207719-1_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5207719-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5207719-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Environmental Compliance

[MD_5207719-1_0404201836_dmtec](#)

English

[MD_5207719-1_0404201836_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English