




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Mounting Screw**

Screw Length: 12.85 mm [.506 in]

Features

Product Type Features

| | |
|--------------------------------|----------------|
| Product Type | Accessory |
| D-Shaped Connector Accessories | Mounting Screw |

Mechanical Attachment

| | |
|--------------------------|-------------------|
| Screw Finish | Clear Chromate |
| Screw & Hole Thread Size | 4-40 |
| Screw Length | 12.85 mm[.506 in] |

Dimensions

| | |
|---------------|------------------|
| Thread Length | 5.31 mm[.209 in] |
|---------------|------------------|

Packaging Features

| | |
|--------------------|---------|
| Packaging Quantity | 1 |
| Packaging Method | Package |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in Component Part) |



Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

| | |
|---------------------------|---|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5206052-3
SCREW,SPECIAL,ZN



TE Part # 5745833-5
CABLE CLAMP KIT,SZ 3

Also in the Series | AMPLIMITE Kit



D-Sub Backshells & Clamps(136)



D-Sub Contact Accessories(1)













D-Sub Covers(3)



D-Sub Locking & Mounting(122)

Customers Also Bought



| | | | |
|---|--|--|---|
|  <p>TE Part #1705549-1 Invertible Modular Jack 8P shielded</p> |  <p>TE Part #160252-2 RING TONGUE IS AUTOMATIC 0.5-1.43MM2TPBR</p> |  <p>TE Part #1879215-2 CPF 0402 4K12 0.1% 25PPM 1K RL</p> |  <p>TE Part #134752-3 KIT CAPOT HD-20 9P</p> |
|  <p>TE Part #1-2176363-6 RQ 0402 619R 0.1% 10PPM 5K RL</p> |  <p>TE Part #1565917-4 DDR2 SO DIMM Sockets</p> |  <p>TE Part #YDTS26G17-08SNV001 D38999: Straight Plug, 17-08 Insert</p> |  <p>TE Part #1-1649329-5 RT424024</p> |
|  <p>TE Part #1-539783-0 DIE MCP9,5 16MM EDS</p> |  <p>TE Part #1-5021101-2 SCREW, MACHINE, FILLISTER HEAD, SLOT</p> | | |

Documents

Product Drawings
MOUNTING SCREW, ZN PLTD
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5747971-3_O.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5747971-3_O.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5747971-3_O.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Environmental Compliance



Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English