



POWER BANK 20 000 mAh

BL-120PB/1VH

KEY FEATURES




- ✓ **100 years of brand history**
Rich heritage & German quality
- ✓ **20 000 mAh capacity**
- ✓ **1x USB-C with 20W fast charge**
2x USB-A with 20W fast charge
- ✓ **Power Delivery 3.0**
Qualcomm 3.0 Quick Charge
- ✓ **High quality fabric and materials**
- ✓ **USB-A/USB-C cable included**
- ✓ **Flight proved**
Overcharge and overvoltage protection



LOGISTIC INFORMATION	Model name: BL-120PB/1VH; Code: 30010238; EAN: 5410853069560; CSU per CAR: 10 CSU;
CAPACITY	20 000 mAh; Up to 4 full smartphone charge of energy*;
CHARGING TECHNOLOGY	Up to 20W; 50% in 25 min* ; Power Delivery 3.0; Qualcomm Quick Charge 3.0
DIMENSIONS	POWERBANK size and weight: 156mm x 78mm x 22.6mm 430g; CSU size and weight: 185mm x 105mm x 29mm 462g;
PORTS	Input/Output: 1x USB-C 5V/3A, 9V/2A, 12V/1.5A; Output: 1x USB-C 5V/3A, 9V/2A, 12V/1.5A 2x USB-A 5V/2.4A, 9V/2A, 12V/1.5A; Charging 2 devices at once ;

*Based on iPhone 14 and iPhone 14 Pro



POWERFUL AND FAST

Your go-to 20 000 mAh powerbank for simultaneous charging of your everyday devices with fast charge solutions.

Not just smartphones, this powerbank is suitable for all of your must-have gadgets such as **tablets**, **wearables (including smartwatches)** and **headphones**.



PORTFOLIO COMPARISON



BL-105PB/1VH



BL-110PB/1VH



BL-110WPB/1VH



BL-120PB/1VH

CAPACITY	5 000 mAh	10 000 mAh	10 000 mAh	20 000 mAh
POWER DELIVERY	Up to 12W	Up to 20W	Up to 20W	Up to 20W
IMPUTS	1 x USB C 1 x USB A	1 x USB C 2 x USB A	1 x USB C 1 x USB A	1 x USB C 2 x USB A
WIRELESS CHARGING	-	-	yes	-
COMPATIBLE FAST-CHARGING	P.D. 3.0 Qualcomm Quick Charge 3.0	P.D. 3.0 Qualcomm Quick Charge 3.0	P.D. 3.0 Qualcomm Quick Charge 3.0 Qi Wireless charging	P.D. 3.0 Qualcomm Quick Charge 3.0