

Technical data sheet

Actuator sensor interface · USB-panel connector

HDMI 2.0 panel connector for front installation PG21, shielded Female Type A / Female Type A / 180° / 1:1



Identification

Type	HDMI F/F 180° PC
Part No.	493090

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Application	• Service interface for control cabinets and control panels
Properties	• Very compact and durable design • Transparent hinged lid, locks in place when opened • High protection class IP69 • Straight connector 180° • Installation depth approx. 100 mm • Can be sealed with a lead seal • Can be labeled with a description plate

General

Design	HDMI 2.0
Form male 1	HDMI Type A female
Form male 2	HDMI Type A female
Degree of pollution	3
Insulation resistance	>100 MΩ
Contact resistance	<30 mΩ
Degree of protection	IP65/67/68/69 in closed and IP20 in inserted position
Housing material	PC, ABS
Contact material	CuSn, gold-plated

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0
www.luetze.de • info@luetze.de

19.06.2024 • Subject to technical modification

Part No. [493090](#) • Datasheet version: 00

page 1 of 4

Technical data sheet

Actuator sensor interface · USB-panel connector

Mounting	Front installation
Installation depth	approx. 100 mm
Operation temperature range	-20 °C ... +80 °C
Storage temperature range	-20 °C ... +80 °C
Dimensions (w × h × d)	31.0 mm × 38.6 mm × 44.5 mm
Mechanical service life	≥1000 insertion cycles
Weight/unit	0.028 kg
PU (units)	1

Technical data

Rated voltage U_N	AC/DC 5 V
Max. Power	2.5 W
Operating voltage max.	30 V
Rated current	0.5 A
Pole number	19
Bandwidth	4 K / 60 Hz
Transfer rate	18 Gbit/s
Contact type	1 : 1


Equipment/Spare parts

Accessories

Not included in the delivery:

Labelling sign 5×5 mm, white: Part.-No. 716431 | LOCC-Box-BZW 7-6431 |
PU: 1 unit (200 tabs)

Dimensions



Actuator sensor interface · USB-panel connector


Technical drawing of a circular part. The drawing shows a circle with a horizontal centerline and a vertical centerline. The dimensions are:

- Vertical dimension: $26,1^{+0,2}_{-0}$
- Horizontal dimension: $\varnothing 28,5^{+0,2}_{-0}$

Pin layout

HDMI female

HDMI female



Circuit diagram

