

Data sheet | Item number: 772-269

Tap-off module; with phase selection; 3-pole; for WINSTA® MIDI connectors and distribution connectors; position on supply L2; Coding P




www.wago.com/772-269



RoHS Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:



Data
Electrical data

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	400 V
Rated impulse voltage (III / 3)	6 kV
Rated current	25 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

Connection data

Connection technology	IDC
Actuation type	Operating tool
No. of poles	3
Total number of potentials	3

Geometrical Data

Width	49 mm / 1.929 inch
Height	46.5 mm / 1.831 inch
Depth	79 mm / 3.11 inch

Mechanical data

Coding	P
Mating force of a plug-in connection	approx. 30–70N (depending on number of poles)
Unmating force of a plug-in connection	when unlocked: approx. 15–20N
Marking	L N
Degree of protection	IP20
Potential marking	L N

Plug connection

Mismating protection	Yes
Locking of plug-in connection	locking lever

Material Data

Color	red
Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0
Contact material	Copper or copper alloy, surface-treated
Fire load	1.833 MJ
Weight	69.722 g

Environmental Requirements

Surrounding air (operating) temperature	-35 ... 85 °C
---	---------------

Commercial data

Country of origin	DE
GTIN	4045454599539
Customs Tariff No.	85366990990
Product Group	20 (WINSTA)

Compatible products

assembling



Item no.: 772-260
Mounting plate; for power supply and tap-off modules

www.wago.com/772-260

wiring and connectors

	Item no.: 897-251 Flat cable; PVC insulated; 5 x 2.5 mm ²	www.wago.com/897-251
	Item no.: 897-252 Flat cable; halogen-free; 5 x 2.5 mm ²	www.wago.com/897-252
	Item no.: 897-261 Flat cable; PVC insulated; 5 x 2.5 mm ² + 2 x 1.5 mm ²	www.wago.com/897-261
	Item no.: 897-262 Flat cable; halogen-free; 5 x 2.5 mm ² + 2 x 1.5 mm ²	www.wago.com/897-262
	Item no.: 897-453 Flat cable; halogen-free; 5 x 4 mm ²	www.wago.com/897-453

protection

	Item no.: 770-201 Lockout cap; for socket; 12-pole; separable	www.wago.com/770-201
	Item no.: 770-221 Lockout cap; for socket; 12-pole; separable	www.wago.com/770-221

tools

	Item no.: 210-635 Operating tool; short version; Blade (6.5 x 1.2) mm	www.wago.com/210-635
	Item no.: 210-636 Operating tool with partially insulated shaft; Blade (6.5 x 1.2) mm	www.wago.com/210-636

Downloads

Documentation

Bid Text

772-269	Sep 22, 2016	DOC	Download
WINSTA IDC		23.0 kB	

Subject to changes.