


ES APG 80 WM 95**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Version	95mm ² , WM crimp
Order No.	1502530000
Type	ES APG 80 WM 95
GTIN (EAN)	4050118310566
Qty.	1 items

ES APG 80 WM 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	304.48 g
------------	----------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	12 mm	Crimp cross-section copper	95
Crimping width in mm	12		

Description of contact

Conductor cross-section, max. AWG	3/0	Conductor cross-section, min. AWG	3/0
Crimping range, max.	95 mm ²		

tool data crimping

Crimping type/profile	WM crimp
Cable lug cross section	nominal 95 mm ²

Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90
ECLASS 13.0	21-04-90-90	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES APG 80 WM 95

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Type	APG 80	Version
Order No.	1502390000	6mm ² , 400mm ²
GTIN (EAN)	4050118310627	
Qty.	1 ST	

95 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M6/-95	Version
Order No.	1495820000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305531	
Qty.	25 ST	
Type	KRN-M8/-95	Version
Order No.	1495600000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305241	
Qty.	25 ST	
Type	KRN-M10/-95	Version
Order No.	1495610000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305371	
Qty.	25 ST	
Type	KRN-M12/-95	Version
Order No.	1495620000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305265	
Qty.	25 ST	
Type	KRN-M14/-95	Version
Order No.	1495780000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305555	
Qty.	25 ST	

ES APG 80 WM 95

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KRN-M16/-95	Version
Order No.	1495630000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305326	
Qty.	25 ST	
Type	KRN-M20/-95	Version
Order No.	1495640000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305319	
Qty.	25 ST	
Type	KRN-M6/-95 S	Version
Order No.	1494430000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118303957	
Qty.	25 ST	
Type	KRN-M8/-95 S	Version
Order No.	1494890000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118304121	
Qty.	25 ST	
Type	KRN-M10/-95 S	Version
Order No.	1494900000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118304398	
Qty.	25 ST	
Type	KRN-M12/-95 S	Version
Order No.	1494910000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118304510	
Qty.	25 ST	
Type	KWN-M8/-95 90	Version
Order No.	1496080000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305685	
Qty.	25 ST	
Type	KWN-M10/-95 90	Version
Order No.	1496090000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305692	
Qty.	25 ST	
Type	KWN-M12/-95 90	Version
Order No.	1496100000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305487	
Qty.	25 ST	
Type	KWN-M14/-95 90	Version
Order No.	1494670000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118304411	
Qty.	25 ST	
Type	KWN-M16/-95 90	Version
Order No.	1496110000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305678	
Qty.	25 ST	
Type	KWN-M8/-95 45	Version
Order No.	1496340000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118305821	
Qty.	25 ST	
Type	KWN-M10/-95 45	Version
Order No.	1496350000	cable lug, terminal end, 95 mm ² , 95 mm ² - 95 mm ²
GTIN (EAN)	4050118306125	
Qty.	25 ST	

ES APG 80 WM 95

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KWN-M12/-95 45	Version
Order No.	1496370000	cable lug, terminal end,95 mm²,95 mm² - 95 mm²
GTIN (EAN)	4050118305890	
Qty.	25 ST	
Type	KWN-M16/-95 45	Version
Order No.	1496380000	cable lug, terminal end,95 mm²,95 mm² - 95 mm²
GTIN (EAN)	4050118305838	
Qty.	25 ST	
Type	VSTN/-95	Version
Order No.	1494770000	cable lug, terminal end,95 mm²,95 mm², None
GTIN (EAN)	4050118304220	
Qty.	50 ST	
Type	KP-M8/-95	Version
Order No.	1498180000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307498	
Qty.	50 ST	
Type	KP-M10/-95	Version
Order No.	1498190000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307603	
Qty.	50 ST	
Type	KP-M12/-95	Version
Order No.	1498210000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307610	
Qty.	50 ST	
Type	KP-M14/-95	Version
Order No.	1498520000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307863	
Qty.	50 ST	
Type	KP-M16/-95	Version
Order No.	1498220000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307719	
Qty.	50 ST	
Type	KP-M20/-95	Version
Order No.	1498230000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307634	
Qty.	50 ST	
Type	KWPN-M8/-95 90	Version
Order No.	1497690000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307207	
Qty.	25 ST	
Type	KWPN-M10/-95 90	Version
Order No.	1497710000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307139	
Qty.	25 ST	
Type	KWPN-M12/-95 90	Version
Order No.	1497720000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307214	
Qty.	25 ST	
Type	KWPN-M16/-95 90	Version
Order No.	1497730000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118307054	
Qty.	25 ST	

ES APG 80 WM 95

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	VPN/-95	Version
Order No.	1498680000	cable lug, terminal end,95 mm²,95 mm²,None
GTIN (EAN)	4050118307917	
Qty.	50 ST	
Type	KQN-M8/-95	Version
Order No.	1493260000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118303162	
Qty.	25 ST	
Type	KQN-M10/-95	Version
Order No.	1493270000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118303018	
Qty.	25 ST	
Type	KQN-M12/-95	Version
Order No.	1493280000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118302899	
Qty.	25 ST	
Type	KQN-M16/-95	Version
Order No.	1493290000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118303025	
Qty.	25 ST	
Type	KQN-M20/-95	Version
Order No.	1493310000	cable lug, terminal end,95 mm²
GTIN (EAN)	4050118303407	
Qty.	25 ST	
Type	KSN/-95	Version
Order No.	1492840000	cable lug, terminal end,95 mm²,95 mm²
GTIN (EAN)	4050118302790	
Qty.	25 ST	
Type	VPLN/-95	Version
Order No.	1492950000	cable lug, terminal end,95 mm²,95 mm²,None
GTIN (EAN)	4050118302622	
Qty.	50 ST	
Type	VSTN/95	Version
Order No.	1493090000	cable lug, terminal end,95 mm²,95 mm²,None
GTIN (EAN)	4050118302929	
Qty.	50 ST	