


ES APG 80 WM 70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Version	70mm ² , WM crimp
Order No.	1502520000
Type	ES APG 80 WM 70
GTIN (EAN)	4050118310580
Qty.	1 items

ES APG 80 WM 70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	342.3 g
------------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	12 mm	Crimp cross-section copper	70
Crimping width in mm	12		

Description of contact

Conductor cross-section, max. AWG	2/0	Conductor cross-section, min. AWG	2/0
Crimping range, max.	70 mm ²		

tool data crimping

Crimping type/profile	WM crimp
Cable lug cross section	nominal 70 mm ²

Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90
ECLASS 13.0	21-04-90-90	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES APG 80 WM 70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Type	APG 80	Version
Order No.	1502390000	6mm ² , 400mm ²
GTIN (EAN)	4050118310627	
Qty.	1 ST	

70 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M6/-70	Version
Order No.	1496640000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305951	
Qty.	25 ST	
Type	KRN-M8/-70	Version
Order No.	1496650000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305791	
Qty.	25 ST	
Type	KRN-M10/-70	Version
Order No.	1496670000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305845	
Qty.	25 ST	
Type	KRN-M12/-70	Version
Order No.	1495570000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118304992	
Qty.	25 ST	
Type	KRN-M14/-70	Version
Order No.	1495770000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305166	
Qty.	25 ST	

ES APG 80 WM 70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KRN-M16/-70	Version
Order No.	1495580000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118305340	
Qty.	25 ST	
Type	KRN-M20/-70	Version
Order No.	1495590000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118305302	
Qty.	25 ST	
Type	KRN-M6/-70 S	Version
Order No.	1494850000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118304152	
Qty.	25 ST	
Type	KRN-M8/-70 S	Version
Order No.	1494860000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118304527	
Qty.	25 ST	
Type	KRN-M10/-70 S	Version
Order No.	1494870000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118304503	
Qty.	25 ST	
Type	KRN-M12/-70 S	Version
Order No.	1494880000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118304435	
Qty.	25 ST	
Type	KWN-M6/-70 90	Version
Order No.	1496010000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118305609	
Qty.	25 ST	
Type	KWN-M8/-70 90	Version
Order No.	1496020000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118305180	
Qty.	25 ST	
Type	KWN-M10/-70 90	Version
Order No.	1496030000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118305432	
Qty.	25 ST	
Type	KWN-M12/-70 90	Version
Order No.	1496040000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118305463	
Qty.	25 ST	
Type	KWN-M14/-70 90	Version
Order No.	1494660000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118304183	
Qty.	25 ST	
Type	KWN-M16/-70 90	Version
Order No.	1496050000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118305708	
Qty.	25 ST	
Type	KWN-M20/-70 90	Version
Order No.	1496070000	cable lug, terminal end, 70 mm², 70 mm² - 70 mm²
GTIN (EAN)	4050118305661	
Qty.	25 ST	

ES APG 80 WM 70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KWN-M8/-70 45	Version
Order No.	1496310000	cable lug, terminal end,70 mm²,70 mm² - 70 mm²
GTIN (EAN)	4050118305944	
Qty.	25 ST	
Type	KWN-M10/-70 45	Version
Order No.	1496320000	cable lug, terminal end,70 mm²,70 mm² - 70 mm²
GTIN (EAN)	4050118306255	
Qty.	25 ST	
Type	KWN-M12/-70 45	Version
Order No.	1496330000	cable lug, terminal end,70 mm²,70 mm² - 70 mm²
GTIN (EAN)	4050118305586	
Qty.	25 ST	
Type	VSTN/-70	Version
Order No.	1494760000	cable lug, terminal end,70 mm²,70 mm²,None
GTIN (EAN)	4050118304299	
Qty.	50 ST	
Type	KP-M8/-70	Version
Order No.	1498130000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307351	
Qty.	50 ST	
Type	KP-M10/-70	Version
Order No.	1498140000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307429	
Qty.	50 ST	
Type	KP-M12/-70	Version
Order No.	1498150000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307467	
Qty.	50 ST	
Type	KP-M14/-70	Version
Order No.	1498560000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307696	
Qty.	50 ST	
Type	KP-M16/-70	Version
Order No.	1498160000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307481	
Qty.	50 ST	
Type	KP-M20/-70	Version
Order No.	1498170000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307344	
Qty.	50 ST	
Type	KWPN-M8/-70 90	Version
Order No.	1497640000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307047	
Qty.	25 ST	
Type	KWPN-M10/-70 90	Version
Order No.	1497650000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307177	
Qty.	25 ST	
Type	KWPN-M12/-70 90	Version
Order No.	1497660000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307092	
Qty.	25 ST	

ES APG 80 WM 70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KWPN-M16/-70 90	Version
Order No.	1497680000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118307122	
Qty.	25 ST	
Type	VPN/-70	Version
Order No.	1498670000	cable lug, terminal end,70 mm²,70 mm²,None
GTIN (EAN)	4050118308020	
Qty.	50 ST	
Type	KQN-M6/-70	Version
Order No.	1493190000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118303261	
Qty.	50 ST	
Type	KQN-M8/-70	Version
Order No.	1493210000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118302875	
Qty.	50 ST	
Type	KQN-M10/-70	Version
Order No.	1493220000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118302882	
Qty.	50 ST	
Type	KQN-M12/-70	Version
Order No.	1493230000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118303032	
Qty.	50 ST	
Type	KQN-M16/-70	Version
Order No.	1493240000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118303131	
Qty.	50 ST	
Type	KQN-M20/-70	Version
Order No.	1493250000	cable lug, terminal end,70 mm²
GTIN (EAN)	4050118303087	
Qty.	50 ST	
Type	KSN/-70	Version
Order No.	1492830000	cable lug, terminal end,70 mm²,70 mm²
GTIN (EAN)	4050118302585	
Qty.	50 ST	
Type	VPLN/-70	Version
Order No.	1492940000	cable lug, terminal end,70 mm²,70 mm²,None
GTIN (EAN)	4050118302738	
Qty.	100 ST	
Type	VSTN/70	Version
Order No.	1493080000	cable lug, terminal end,70 mm²,70 mm²,None
GTIN (EAN)	4050118302967	
Qty.	50 ST	