



Item number/name **136624**

**Compact 62**

EAN unitnumber 5733439136624

Colour raaco Blue

Description of the item

Compact 62 incl. 10 assorted inserts and divider. Weight 7,1 kg. Toolbox made of PP. Flexible arrangement of compartments using inserts. 4 drawers for small items. Castors or a carrying strap can be fitted. (Available separately).

BOM items

| <u>Item number</u> | <u>Product</u>                     | <u>Quantity</u> |
|--------------------|------------------------------------|-----------------|
| 230735             | Kasse C.62                         | 1               |
| 230049             | FEET COMPA                         | 4               |
| 230544             | Håndtag C.37/62 Gassmelt           | 2               |
| 230810             | Sideføring. Mont C.62 Compact 62   | 2               |
| 230827             | Midterføring. Mont C.62 Compact 62 | 2               |
| 274395             | BOTTOM PL.COM62                    | 1               |
| 274388             | DIV COMPA 62                       | 1               |
| 230209             | Skuffe Compa 62                    | 4               |
| 278270             | MONT. TRAY 50/62 10 INS.           | 1               |
| 229357             | LID+HDL. 50/62                     | 2               |

Materials

| <u>Item number</u> | <u>Material</u>         |
|--------------------|-------------------------|
| 600170             | Polypropylene - PP      |
| 600033             | Other granulates        |
| 600026             | Other granulates        |
| 600019             | Polystyrene impact - SB |
| 600132             | Polypropylene - PP      |
| 600194             | Polypropylene - PP      |

Item dimensions

|                         |       |
|-------------------------|-------|
| Net. Depth (mm) .....   | 311,0 |
| Net. Width (mm) .....   | 621,0 |
| Net. Height (mm) .....  | 322,0 |
| Inner Depth (mm) .....  | 245,0 |
| Inner Width (mm) .....  | 537,0 |
| Inner Height (mm) ..... | 155,0 |

Weight

|                          |       |
|--------------------------|-------|
| Net weight (Kgs) .....   | 6,475 |
| Tare weight (Kgs) .....  | 0,660 |
| Gross weight (Kgs) ..... | 7,135 |

Volume

|                         |         |
|-------------------------|---------|
| Multiple (Pieces) ..... | 1,00    |
| Volume (m3) .....       | 0,06620 |

Capacity load

|                         |       |
|-------------------------|-------|
| Carr. Load (Kgs) .....  | 50,00 |
| Carr. Load (Ltrs) ..... | 30,60 |

**Sales**

raaco Great Britain Ltd  
VAT No.: GB 232 6219 86  
Wenrisc House, Meadow Court  
High Street, Witney  
Oxfordshire OX28 6ER  
Tel: (01993) 776333  
Fax: (01993) 776444

**Headquarters:**

raaco A/S  
CVR No.: DK 22 12 28 19  
VAT No.: DK 91 42 64 55  
Platanvej 19  
DK-4800 Nykøbing F  
Tel.: +45 54 88 84 00