

CD 60X25 4/6 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Well-structured and protected wiring provides the basis for installation, maintenance, and safe operation. Those requirements apply in particular for explosion-protected areas. According to DIN EN 60079-14 these wiring ducts are suitable for cables containing intrinsically safe circuits.

General ordering data

Version	60 mm x 25 mm, 4.00 mm x 6.00 mm, 2000 mm
Order No.	2662600000
Type	CD 60X25 4/6 BL
GTIN (EAN)	4050118685169
Qty.	40 M
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31T00:00:00+01:00

CD 60X25 4/6 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	60 mm	Height (inches)	2.3622 inch
Width	25 mm	Width (inches)	0.9842 inch
Length	2000 mm	Length (inches)	78.74 inch
Net weight	355 g		

Temperatures

Operating temperature range	-5...60 °C
-----------------------------	------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

UL 94 flammability rating	V-0	Colour	blue
Halogen	Yes	Standards	In accordance with DIN EN 50085
Basic material	PVC / lead-free	Version of side panel	slotted
Slit gap	6.00 mm	Slit width	4.00 mm
Lid	Yes	Operating temperature range	-5...60 °C
Included in delivery	Cable duct, Lid		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ETIM 10.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03	ECLASS 13.0	27-40-07-03
ECLASS 14.0	27-40-07-03	ECLASS 15.0	27-40-07-03

CD 60X25 4/6 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.




General ordering data

Type	EXRV 4.5	Version
Order No.	2562700000	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1000 ST	
Type	EXRV 6.5	Version
Order No.	2562690000	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1000 ST	
Type	EXRV-T 4.5	Version
Order No.	2562720000	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 ST	
Type	EXRV-T 6.5	Version
Order No.	2562710000	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 ST	

Marking

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



General ordering data

Type	CD-LBH	Version
Order No.	2562850000	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 ST	
Type	CD-LB	Version
Order No.	2562680000	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 ST	

CD 60X25 4/6 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	CD-LBK	Version
Order No.	2554120000	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 ST	

Side arm

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Type	CD-RETA	Version
Order No.	2554080000	Cable duct binder arm, 8 mm x 115.3 mm
GTIN (EAN)	4050118564204	
Qty.	100 ST	