

RAACOSTAT



▲ A wide range of mobile ESD products. All stationary products are equipped with earth leads

Full protection of electronic components

RAACOSTAT ensures efficient, anti-static protection for sensitive equipment.

A rapidly increasing number of products, spare parts, tools, etc., are composed of electronic components, which are often incredibly sensitive to the damage caused by static electricity. This damage can occur not only during the actual production process, but also when the items are stored, transported, etc.

RAACOSTAT is a complete series of boxes, tool trays, shelving and drawers that can provide 100 percent protection against static electricity. Like all other raaco products, the RAACOSTAT series is naturally capable of being combined in numerous different ways, to meet almost any individual need.

RAACOSTAT has shown its value in practice in a wide range of companies around the world. The reports all agree: fault percentages have fallen off markedly thanks to the use of RAACOSTAT products. As a consequence, the efficiency of these companies has risen correspondingly.

The RAACOSTAT series is constructed of a special plastic containing carbon fibres, which makes the products permanently anti-static. This protection will not diminish over time or through intensive use, and neither will weather conditions or the surroundings in general have any effect on its efficiency.


RAACOSTAT naturally fulfils the EN 61340-5-1 standard and all other international requirements. Surface resistance: 10 (4)-10 (9) Ω .



All stationary products are supplied with earth leads ▶



ESD inserts enable flexible organisation. The inserts fit several different products ▶



The design of the Storage bins ensures easy access to the contents – even with the smallest bins ▶



Wall panels can be fitted rapidly and easily ▶



RAACOSTAT 150 CABINET

1260-00 ESD

Colour: Galvanized/Black
HxWxD, mm: 552x306x150
Units per carton: 1
EAN-no.: 102513



ESD Cabinet with 60 drawers, type 150-00. Each drawer can be divided into 2 compartments. See page 39. Earth wire included.

1248-01 ESD

Colour: Galvanized/Black
HxWxD, mm: 552x306x150
Units per carton: 1
EAN-no.: 102520



ESD Cabinet with 48 drawers, type 150-01. Each drawer can be divided into 6 compartments. See page 39. Earth wire included.

1224-02 ESD

Colour: Galvanized/Black
HxWxD, mm: 552x306x150
Units per carton: 1
EAN-no.: 102537



ESD Cabinet with 24 drawers, type 150-02. Each drawer can be divided into 3 compartments. See page 39. Earth wire included.

DC 1200 ESD

Colour: Galvanized/Black
HxWxD, mm: 1760xØ680
Units per carton: 1
EAN-no.: 102568



Turntable-empty. Can be fitted with any 12 x ESD 1200 series cabinets. Earth wire included.

945-00 ESD

Colour: Galvanized/Black
HxWxD, mm: 417x306x150
Units per carton: 1
EAN-no.: 118231



ESD Cabinet with 45 drawers, type 150-00. Each drawer can be divided into 2 compartments. See page 39. Earth wire included.

936-01 ESD

Colour: Galvanized/Black
HxWxD, mm: 417x306x150
Units per carton: 1
EAN-no.: 109246



ESD Cabinet with 36 drawers, type 150-01. Each drawer can be divided into 6 compartments. See page 39. Earth wire included.

918-02 ESD

Colour: Galvanized/Black
HxWxD, mm: 417x306x150
Units per carton: 1
EAN-no.: 102544



ESD Cabinet with 18 drawers, type 150-02. Each drawer can be divided into 3 compartments. See page 39. Earth wire included.

DC 900 ESD

Colour: Galvanized/Black
HxWxD, mm: 1600xØ680
Units per carton: 1
EAN-no.: 102964



Turntable-empty. Can be fitted with any 12 x ESD 900 series cabinets. Earth wire included.