

## BIT E6.3 Z 0.8X4.0X39


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

### General ordering data

|            |                                                                                             |
|------------|---------------------------------------------------------------------------------------------|
| Version    | Screwdriver insert, Blade width (B): 4 mm, Blade length: 39 mm, Blade thickness (A): 0.8 mm |
| Order No.  | <a href="#">2749030000</a>                                                                  |
| Type       | BIT E6.3 Z 0.8X4.0X39                                                                       |
| GTIN (EAN) | 4050118895322                                                                               |
| Qty.       | 5 items                                                                                     |

**BIT E6.3 Z 0.8X4.0X39**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |                |             |
|------------|--------|----------------|-------------|
| Width      | 39 mm  | Width (inches) | 1.5354 inch |
| Net weight | 4.35 g |                |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Technical data**

|                        |                    |
|------------------------|--------------------|
| Description of article | Bit with pilot tip |
|------------------------|--------------------|

**Screwing tools**

|                 |                                            |                     |        |
|-----------------|--------------------------------------------|---------------------|--------|
| Blade width (B) | 4 mm                                       | Blade thickness (A) | 0.8 mm |
| Form            | E 6.3 DIN 3126, With assembly peg, Slotted | Blade length        | 39 mm  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002116    | ETIM 7.0    | EC002116    |
| ETIM 8.0    | EC003864    | ETIM 9.0    | EC003864    |
| ETIM 10.0   | EC003864    | ECLASS 9.1  | 21-04-04-90 |
| ECLASS 10.0 | 21-04-04-90 | ECLASS 11.0 | 21-04-42-04 |
| ECLASS 12.0 | 21-04-42-04 | ECLASS 13.0 | 21-04-42-04 |
| ECLASS 14.0 | 21-04-42-04 | ECLASS 15.0 | 21-04-42-04 |