

D connectors


Order code	Manufacturer code	Description
15-0800	DPPK-9-BLACK	9 WAY SNAP FIT BLACK D COVER (RC)
15-0805	DPPK-9-RED	9 WAY RED D CONNECTOR COVER (RC)
15-0810	DPPK-9-BLUE	9 WAY BLUE D CONNECTOR COVER (RC)
15-0815	DPPK-9-YELLOW	9 WAY YELLOW D CONNECTOR COVER (RC)
15-0820	DPPK-9-LT. GREY	9W LT.GREY D CONNECTOR COVER (RC)
15-0825	DPPK-9-IVORY	9 WAY IVORY D CONNECTOR COVER (RC)
15-0860	DPPK-15-BLACK	15 WAY BLACK D CONNECTOR COVER (RC)
15-0865	DPPK-15-RED	15 WAY RED D CONNECTOR COVER (RC)
15-0870	DPPK-15-BLUE	15 WAY BLUE D CONNECTOR COVER (RC)
15-0875	DPPK-15-YELLOW	15 WAY YELLOW D CONN.COVER (RC)
15-0880	DPPK-15-LT. GREY	15W LIGHT GREY D CONN.COVER (RC)
15-0885	DPPK-15-IVORY	15W IVORY D CONNECTOR COVER (RC)
15-0930	DPPK-25-BLACK	25W BLACK D CONNECTOR COVER (RC)
15-0935	DPPK-25-RED	25 WAY RED D CONNECTOR COVER (RC)
15-0940	DPPK-25-BLUE	25 WAY BLUE D CONNECTOR COVER (RC)
15-0945	DPPK-25-YELLOW	25W YELLOW D CONNECTOR COVER (RC)
15-0950	DPPK-25-LT. GREY	25W LT.GREY D CONNECTOR COVER (RC)
15-0955	DPPK-25-IVORY	25 WAY IVORY D CONNECTOR COVER (RC)

D connectors	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

Colour Coded D Covers

One-piece snap together design for fast, efficient assembly.

- Manufactured in UL94V-2 rated nylon
- Turned full metal 4-40UNC thumbscrews (other thread sizes available to order)
- Thumbscrew retention features for ease of assembly
- Fast assembly cable clamp with high quality self-tapping screws
- Wide range of colours available for coding/brand identification



Ways	Dim A	Dim B	Max Cable O.D.
9	35.0	17	8.4
15	41.0	16	12
25	54.5	15	12