



Kunststoff-Spannzangen-Knöpfe mit matter Oberfläche




Plastic Collet Knobs with mat-black finished surface Bouton en matière plastic

Drehknopf, Ausführung matt
Collet knobs, Type dull

Ø A	B	C	Ø d	Ø D	Ø E	F	G	schwarz black Art.-Nr.	grau grey Art.-Nr.
12	14	7,5	3 3,2 4	-	-	-	5	4307.3131 4307.1131 4307.4131	4307.3141 4307.1141 4307.4141
15	16	9,5	4 6 6,35	-	-	-	5	4309.4131 4309.6131 4309.7131	4309.4141 4309.6141 4309.7141
20	17	13	4 6 6,35	-	17	2,5	11	4311.4131 4311.6131 4311.7131	4311.4141 4311.6141 4311.7141
28	18,5	17	6 6,35	-	23	4,5	11	4312.6131 4312.7131	4312.6141 4312.7141

Ø A	B	C	Ø d	Ø D	Ø E	F	G	schwarz black Art.-Nr.	grau grey Art.-Nr.
12	18	10,5	3 3,2 4	17	15	2,5	9	4308.3131 4308.1131 4308.4131	4308.3141 4308.1141 4308.4141
15	20	12	4 6 6,35	20	18	2,5	9	4310.4131 4310.6131 4310.7131	4310.4141 4310.6141 4310.7141

Abdeckkappe, flache Ausführung Oberfläche matt



Caps, flat Design Mat surface

Strichanzeige Indicator Mark	Farbe Colour	Abdeckkappen passend zu Knopf-Durchmesser: A Caps fit to Knob-Diameter: A			
		Ø 12	Ø 15	Ø 20	Ø 28
		Art.-Nr.	Art.-Nr.	Art.-Nr.	Art.-Nr.
ohne/without	rot/red	4307.0021	4309.0021	4311.0021	4312.0021
ohne/without	schwarz/black	4307.0031	4309.0031	4311.0031	4312.0031
ohne/without	grau/grey	4307.0041	4309.0041	4311.0041	4312.0041
schwarz/black	rot/red	4307.0121	4309.0121	4311.0121	4312.0121
weiß/white	schwarz/black	4307.0131	4309.0131	4311.0131	4312.0131
schwarz/black	grau/grey	4307.0141	4309.0141	4311.0141	4312.0141

Abdeckplatten in Ausführung matt, bei Bedarf einsetzbar für Drehknöpfe blank.
Caps in mat design, by requirement set in for turning knobs, bright.