




Extra Security Camera

4K ULTRA HD

Add-on Camera for 4K NVR Systems



Extra Camera, More Security

Add this camera to your Swann Professional NVR Series 4K wired security system with the ability to see more detail than before, in amazing Ultra HD



See & Hear in 4K Ultra HD

With 4K Ultra HD video you will be able to see facial detail, license plates, clothing colors & more, while the built-in microphone adds another layer of evidence to your footage



Protection 24/7

Know what's happening at any hour with powerful night vision up to 150ft/45m in total darkness (200ft/60m with ambient light) with a super wide 93° viewing angle & the choice to mount indoors or outdoors



Heat Sensing

Swann's True Detect™ heat & motion-based PIR detection reliably captures & records activity, with fewer false triggers & reliable push notifications



Smart Video Analytics

Video analytics, like Face Detection, Intrusion Detection, Person Detection, Line Crossing & others, recognize visual elements on the screen to trigger recording & alerts



Security Made Smarter

Cut the cost of crime & know what's happening with this robust dome camera to suit homes, offices, small businesses & retail stores

Extra Security Camera

4K ULTRA HD

Add-on Camera
for 4K NVR Systems




See what's happening from anywhere 24/7

A wired security camera that can be added to Swann's Professional NVR-8580 series to see what's happening in 4K Ultra HD & stay connected on your Smartphone



Detect the heat of people & cars

True Detect™ senses the heat from people, cars & large animals to send you push notifications & trigger video recording to a local hard drive. It's truly reliable security!



Know what's happening, faster

The latest smart analytics trigger recording and notify you when activity is sensed, with the ability to detect faces, zone intrusion, line crossing, camera tampering & more



Safeguard loved ones, pets & property

The camera is like another set of eyes allowing you to check in on your family, pets & belongings at any time to see & hear that everything is okay. It's security made smarter!

What's in the box

All installation accessories included

- NHD-886MSD Camera
- Cat5e Ethernet Cable 60ft / 18m
- Mounting Screws & Plugs
- Operating Instructions
- Theft Deterrent Stickers



NHD-886MSD 4K DAY/NIGHT SECURITY CAMERA

Video

Video Quality 4K (3840 x 2160 pixels)
Viewing Angle 93°

Audio

Microphone Yes
Audio Range 16ft / 5m

Night Vision

Night Vision Distance Up to 150ft/45m (Total Darkness)
Up to 200ft/60m (Ambient Light)#
IR Cut Filter Yes


General

PIR Heat / Motion Sensor Yes, True Detect™
PIR Sensor Range Up to 32ft / 10m
Indoor / Outdoor Indoor or Outdoor, IP66 rated
Operating Temperature -22°F ~ 131°F / -30°C ~ 55°C
Body Construction Aluminum
Dimensions – Camera 3.94" x 3.94" / 100mm x 100mm

^ See Swann website for compatible NVRs

Based on adequate ambient light including street lights & house lights, etc.

Note: Trademarks are properties of their respective owners



Thermal-Sensing Technology

- ✓ Reduce false triggers
- ✓ Reliable push notifications
- ✓ Longer recording time

Note: Indicative visual, video images show onscreen like normal



SWNHD-886MSD