

Travel A/V adapter: 3-in-1 Mini DisplayPort to DisplayPort DVI or HDMI converter

StarTech ID: MDP2DPDVHD



The MDP2DPDVHD mini DisplayPort® to DisplayPort®, DVI or HDMI® Multifunction Adapter converts a mini DisplayPort (mDP®) input to DisplayPort, DVI or HDMI output signals - all in a single compact adapter.

This multifunction adapter offers the unique ability to connect almost any display to your mini DisplayPort equipped PC or Mac, providing the perfect solution for business environments that have mixed display hardware - saving the expense of purchasing new displays for compatibility. A plug-and-play solution that requires no software or drivers, this versatile mDP adapter offers a quick and simple installation for the utmost convenience.



Compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt™

I/O port.



This adapter allows for audio pass-through if supported by the video source. Please review the video source manual to confirm support.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Use your existing DVI, HDMI® or DisplayPort® monitors with a new mini DisplayPort® device
- Perfect for IT professionals seeking a solution for connecting mixed display hardware to mini DisplayPort computers

Features

- Adapt Mini DisplayPort to DisplayPort, HDMI or DVI
- Supports resolutions up to 2560x1600 using DisplayPort, 1920x1200 using HDMI/DVI
- No software/drivers required
- Compact design
- Compatible with Intel® Thunderbolt™

Technical Specifications

Warranty	2 Years
Adapter Style	Adapter
Audio	Yes
Converter Type	Travel A/V Adapters
Output Signal	DisplayPort
Output Signal	DVI-D (DVI Digital)
Output Signal	HDMI
Audio Specifications	5.1 Surround Sound
Maximum Digital Resolutions	DisplayPort: 2560x1600 DVI/HDMI; 1920x1200
Connector A	1 - Mini-DisplayPort (20 pin) Male
Connector B	1 - DisplayPort (20 pin) Female
Connector B	1 - DVI-D (25 pin) Female
Connector B	1 - HDMI (19 pin) Female
Humidity	10~85% RH
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-10°C to 80°C (14°F to 176°F)
Cable Length	5.9 in [150 mm]
Color	Black
Enclosure Type	Plastic
Product Height	0.6 in [15 mm]
Product Length	9.4 in [240 mm]
Product Weight	1.6 oz [45 g]
Product Width	1.8 in [45 mm]
Shipping (Package) Weight	0.1 lb [0.1 kg]
Included in Package	1 - MDP to DP/DVI/HDMI Adapter

Certifications, Reports and Compatibility

