

## **HDMI to Composite Converter with Audio**

*StarTech ID: HD2VID*



The HD2VID HDMI® to Composite Video Converter (with Audio) converts a digital HDMI video source (with supporting audio) to work with analog Composite video televisions and displays in both NTSC and PAL systems.

The HDMI to Composite converter provides features that ensure the highest quality output image, such as noise reduction, frame rate conversion and adaptive contrast enhancement, while an easy to use On-Screen Display(OSD) allows you to monitor your display status. Support for a wide range of HDTV and PC input resolutions make this versatile HDMI converter a perfect solution for using newer devices with existing legacy displays.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### **Applications**

- Ideal for converting newer HDMI devices to work with older composite or S-Video televisions
- Great for use in presentations, tradeshow, conferences, retail, entertainment, and home video applications

## Features

- Converts HDMI® source to NTSC or PAL
- Converts HDMI audio to analog stereo RCA Audio
- Supports input HDTV resolutions up to 720p (PC up to 1280x800)
- Output picture size Underscan / Overscan
- Adaptive contrast enhancement
- Supports output resolutions of 480i/576p

Technical Specifications

Warranty	2 Years
Audio	Yes
Converter Type	Scaler
Industry Standards	Standard HDMI, DVI 1.0
Audio Specifications	Input - LPCM 2Ch, 48kHz Output - Stereo L/R
Supported Resolutions	Input TV - 720p, 576p, 480p @ 60Hz PC - 1280x800, 1280x768, 1224x768, 800x600, 640x480 @ 60Hz Output 480i, 576p
Connector A	1 - HDMI (19 pin) Female Input
Connector B	1 - Composite Video (1 x RCA) Female Output
Connector B	1 - Stereo Audio (2 x RCA) Female Output
Center Tip Polarity	Positive
Input Current	0.3 A
Input Voltage	110 ~ 240 AC
Output Current	1A
Output Voltage	5 DC
Plug Type	M
Power Consumption	3W
Power Source	AC Adapter Included
Humidity	20~90% RH
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Color	White
Enclosure Type	Plastic
Product Height	1 in [26 mm]
Product Length	3.9 in [100 mm]
Product Weight	3.2 oz [90 g]
Product Width	2.5 in [64 mm]
Shipping (Package) Weight	0.7 lb [0.3 kg]
Included in Package	1 - HDMI® to Composite Converter
Included in Package	1 - Universal Power Adapter (NA/UK/EU/AU)

Included in Package      1 - Instruction Manual

**Certifications, Reports and Compatibility**

