

4-to-1 HDMI Video Switch with Remote Control

StarTech ID: VS410HDMIE



This 4 port HDMI® Switch lets you connect up to four HDMI-enabled output devices to a single HDMI input - eliminating the need to manually exchange cables to switch between high definition audio video sources.

The HDMI switch fully supports High Speed HDMI device connections, as well as Dolby Digital TrueHD and DTS-HD high definition audio formats and display resolutions up to 1080p(hdtv) / 1920x1200(computer), ensuring a high quality audio and video experience. Suitable for long distance connections, the switch offers a signal enhancement feature that can be used with longer cable connections, boosting the HDMI signal for optimized quality.

The switch provides an economical solution for connecting multiple HDMI out devices (Blu-Ray players, DVD Players, etc.) to a single port on a high definition LCD/Plasma TV.

Applications

- Ideal for home theater situations where you have run out of inputs on your current television to accommodate all of your devices
- Great for use in presentations, trade shows, conferences, retail, and entertainment applications where multiple source devices are required
- Use for video wall setups in retail environments to support several input sources and make them easily switchable
- Perfect for professional A/V test benches testing multiple devices
- Excellent solution for connecting and switching between multiple PCs to one display

Features

- Easy to use remote control for switching between devices
- Supports HDTV resolutions from 480i to 1080p
- Supports PC resolutions from 640x480 to 1920x1200
- High Speed HDMI®, HDCP 1.1, and DVI 1.0 compliant
- Dolby Digital TrueHD and DTS-HD audio

Technical Specifications

| | |
|---------------------------|---|
| Warranty | 2 Years |
| Audio | Yes |
| Ports | 4 |
| Audio Specifications | Supports Dolby Digital TrueHD and DTS-HD |
| Bandwidth | 2.25Gbps (Single Link) |
| Color Depth | 30/36-bit Deep Color |
| Maximum Cable Length | 65.6 ft [20 m] |
| Supported Resolutions | HDTV - 480i~1080p PC - 640x480~1920x1200 |
| Connector A | 4 - HDMI (19 pin) Female |
| Connector B | 1 - HDMI (19 pin) Female |
| Center Tip Polarity | Positive |
| Input Voltage | 110 ~ 240 AC |
| Output Current | 1A |
| Output Voltage | 5 DC |
| Power Source | AC Adapter Included |
| Color | Black |
| Enclosure Type | Plastic |
| Product Height | 1.7 in [44 mm] |
| Product Length | 9.4 in [240 mm] |
| Product Weight | 44.1 oz [1250 g] |
| Product Width | 4.1 in [104 mm] |
| Shipping (Package) Weight | 1.4 lb [0.7 kg] |
| Included in Package | 1 - HDMI® Video Switch |
| Included in Package | 1 - IR Remote Control |
| Included in Package | 1 - Universal Power Adapter (US/UK/EU/AUS) |
| Included in Package | 1 - Instruction Manual |

Certifications, Reports and Compatibility

