

## 7-Port USB 3.0 Hub - Desktop

StarTech ID: *ST7300USB3B*



The ST7300USB3B USB 3.0 Hub lets you add seven external USB 3.0 ports to a computer from a single USB 3.0 host connection.

Offering data transfer rates up to 5 Gbps, the USB hub meets SuperSpeed USB 3.0 specifications and is backward compatible with USB 2.0 and 1.x devices.

Designed for easy port access when connecting or disconnecting devices, the hub features one-sided port orientation, with current overload detection and protection across all seven ports. The hub supports Plug-and-Play and Hot-Swap technologies, letting you switch and operate your connected devices without having to power down the host computer.

The USB hub is bus powered for use in environments where a power outlet may be unavailable, but is perfect for high-power USB devices when used with the included optional power adapter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Expand your system USB 3.0 capabilities with additional ports
- Make USB ports more accessible by positioning the hub anywhere within cable reach
- Extend the range of USB devices by having the hub act as a mid-point repeater
- Separate tightly packed USB ports, to better accommodate larger USB plugs or prevent overcrowding

**Features**

- Seven downstream USB 3.0 ports accessible from one side of the hub
- Compliant with SuperSpeed USB 3.0, with support for up to 5 Gbps
- Plug-and-Play and Hot-Swap compatible
- Backward compatible with USB 2.0 and 1.x devices
- Current overload detection and protection on each USB port
- USB bus powered, includes optional external power adapter for high-power USB devices
- Includes USB 3.0 A to B cable

**Technical Specifications**

Warranty	2 Years
Bus Type	USB 3.0
Chipset ID	VLI - VL812
Fast-Charge Port(s)	No
Ports	7
USB-C Device Port(s)	No
USB-C Host Connection	No
Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s
Connector Type(s)	1 - USB 3.0 B (9 pin; SuperSpeed) Female
Connector Type(s)	7 - USB 3.0 A (9 pin; SuperSpeed) Female
OS Compatibility	OS Independent; No additional drivers or software required
<b>Note</b>	If connected to a USB 2.0 host port, performance may be limited
System and Cable Requirements	Available USB 3.0 port
LED Indicators	7 - Hub Port Connection LEDs
Center Tip Polarity	Positive
Input Current	1.3 A
Input Voltage	100 ~ 240 AC
Output Current	3 A
Output Voltage	12 DC
Plug Type	M
Power Source	AC Adapter Included
Humidity	5-95% RH
Operating Temperature	-2°C to 52°C (29°F to 125°F)
Storage Temperature	-20°C to 56°C (-4°F to 132°F)
Color	Black
Enclosure Type	Plastic
Form Factor	Desktop
Product Height	0.9 in [23 mm]
Product Length	6.8 in [172 mm]
Product Weight	5.2 oz [148 g]
Product Width	2.8 in [70 mm]
Shipping (Package) Weight	19.7 oz [558 g]

Included in Package	1 - USB 3.0 Hub
Included in Package	1 - USB 3.0 Cable
Included in Package	1 - Universal Power Adapter (NA/ UK/ EU)
Included in Package	1 - Instruction Manual

## Certifications, Reports and Compatibility

