

## **6 ft USB to DB25 Parallel Printer Adapter Cable - M/F**

*StarTech ID: ICUSB1284D25*



The ICUSB1284D25 6 ft USB to DB25 Parallel Printer Adapter Cable turns an available USB port on a host PC into a DB25 Female Parallel port - allowing you to connect a DB25 printer to the computer as if the necessary parallel port was built-on.

A cost-effective and reliable solution, the USB to DB25 adapter saves the expense of replacing a parallel printer for the sake of USB capability.

Backed by a StarTech.com 2-year warranty and free lifetime technical support .

### **Applications**

- Allows you to quickly add a parallel port to your computer for use with printers with DB25 connectors
- Ideal solution for notebooks or desktops without a Parallel port

### **Features**

- Fully Plug & Play for easy installation
- USB bus-powered operation, no external power adapter required
- Eliminates the need for manual or automatic parallel switch boxes

## Technical Specifications

|                            |                                                                                                                                                                                     |
|----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Warranty                   | 2 Years                                                                                                                                                                             |
| Bus Type                   | USB 2.0                                                                                                                                                                             |
| Chipset ID                 | Prolific - PL-2305                                                                                                                                                                  |
| Interface                  | Parallel                                                                                                                                                                            |
| Ports                      | 1                                                                                                                                                                                   |
| Maximum Data Transfer Rate | 1.5Mbps                                                                                                                                                                             |
| Connector Type(s)          | 1 - DB-25 (25 pin; D-Sub) Female                                                                                                                                                    |
| Connector Type(s)          | 1 - USB A (4 pin) Male                                                                                                                                                              |
| OS Compatibility           | Windows® 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10<br>Windows Server® 2000, 2003, 2008 R2, 2012, 2012 R2<br>Mac OS X® 10.6 to 10.11<br>Linux 2.6.x to 4.4.x <i>LTS Versions only</i> |
| Humidity                   | 0~80% RH non-condensing                                                                                                                                                             |
| Operating Temperature      | 5°C to 40°C (41°F to 140°F)                                                                                                                                                         |
| Storage Temperature        | -20°C to 70°C (-4°F to 158°F)                                                                                                                                                       |
| Product Length             | 6.1 ft [1.9 m]                                                                                                                                                                      |
| Product Weight             | 3.5 oz [100 g]                                                                                                                                                                      |
| Shipping (Package) Weight  | 0.3 lb [0.1 kg]                                                                                                                                                                     |
| Included in Package        | 1 - USB to Parallel Adapter Cable                                                                                                                                                   |

## Certifications, Reports and Compatibility

