

## DVI Dual-Monitor Docking Station for Laptops - HDMI and VGA Adapters - USB 3.0

StarTech ID: USB3SDOCKDD



This USB 3.0 Laptop Docking Station delivers display flexibility, fast charging, and desktop convenience to your home or office workstation. Using a single connection, the dock instantly adds two DVI ports plus HDMI® and VGA adapters, a USB 3.0 hub with two quick-charge ports, Gigabit Ethernet, and a 3.5mm headset jack to your laptop.

It's the perfect accessory for virtually all USB 3.0 equipped laptops (for example, the Dell™ Latitude 13 7000 2-in-1, Microsoft Surface™ Pro 4, Surface Pro 3, or Surface Book).

### Display Flexibility

Discover multi-monitor freedom! Boost your productivity by adding dual monitor support to your workstation with one of the only docking stations to offer dual DVI video ports each delivering resolutions up to 2048x1152.

For extra display flexibility we've included two DVI video adapters, letting you avoid the frustration and costs of purchasing additional products just to fit the displays you already use. Leave the stress of interface limitations at the door by adapting to the most popular monitor types right out of the box. No hassle, no headaches. With a range of video output options, the dock is ideal for hotel desks or hot desks.





## Device Charging

Charge your mobile devices faster, with or without a laptop connected to the dock. USB charging is convenient, fast, and accessible through two front “always on” USB fast-charge ports, combining data throughput with support for USB Battery Charging Specification 1.2 — You can simultaneously maintain work efficiency while adding charge and sync flexibility for up to two mobile devices (2 tablets or 1 tablet/1 smartphone).

Now, you can easily charge other devices while connected to multiple displays, a Gigabit network, and numerous USB peripherals through the integrated 5-port USB 3.0 controller. Perfect for external USB 3.0 hard drives, the docking station supports UASP-enhanced performance for faster data transfer rates, which means less waiting and more productivity.




## Desktop Convenience

Save time and get more work done! With a single connection to your laptop (e.g. MacBook Pro, MacBook Air, Lenovo® ThinkPad®, HP® or Dell® Ultrabook™) your required peripherals remain connected. Overcome your laptop port limitations and reduce the hassle of constantly reconnecting devices, to create an organized and full-sized workstation with less clutter that's great for hoteling, or hot desking.

Plus, for a clean and customized workspace you can position the docking station in horizontal orientation, or upright (tower), using the included optional stand.

Dual Monitor  
Support



The USB3SDOCKDD is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Applications

- Connect multiple monitors in a variety of flexible display combinations right out-of-the-box: DVI + DVI, DVI + HDMI, DVI + VGA, HDMI + DVI, HDMI + VGA
- Create a shared hoteling workspace or hot desk with an integrated charging station for guests, customers, and colleagues
- Connect a wide variety of peripherals at home / office to a laptop, all from a single USB 3.0 connection
- Neatly set up in mixed environments with upright or horizontal positioning through an included optional stand
- Perfect for use with your MacBook or Ultrabook™, with aesthetically matching silver sand blast housing

## Features

- Dual DVI output; DVI to HDMI and DVI to VGA adapters included
- 2x Front-panel USB 3.0 Fast-charge & Sync ports able to charge devices without a host connection
- Vertical or horizontal dock orientation
- 5x total USB 3.0 data throughput ports with UASP support (2x front ports USB Battery Charging Specification 1.2 compliant, and 3x rear ports)
- Front-panel 3.5mm 4-Position TRRS Headset port - Audio/Microphone
- Gigabit Ethernet RJ45 Port with Wake-on-LAN (WOL)
- Compatible with USB-enabled laptops and Windows based tablets, such as the Microsoft Surface Pro 4 and Surface Book
- Matte silver sand blast finish matching Apple® MacBooks
- Includes 1m flexible and ultra-thin USB 3.0 host cable, stand with screws / screwdriver, and 4x rubber feet
- Front-panel Power LED

**Technical Specifications**

Warranty	2 Years
4K Support	No
Bus Type	USB 3.0
Chipset ID	DisplayLink - DL-3900 (Display, LAN, Audio) Genesys Logic - GL3520 (USB 3.0 w/ Charge)
Displays Supported	2
Fast-Charge Port(s)	Yes
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB Battery Charging Specification Rev. 1.2 USB 3.0 - Hub ports support USB 2.0/1.1 backward-compatibility
Auto MDIX	Yes
Compatible Networks	10/100/1000 Mbps
Full Duplex Support	Yes
Maximum Analog Resolutions	2048x1152 (VGA)
Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	2048x1152 (Dual-Link DVI/HDMI)
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Connector Type(s)	1 - DVI-D (25 pin) Female
Connector Type(s)	1 - DVI-I (29 pin) Female
Connector Type(s)	2 - USB 3.0 A (Fast-Charge; 9 pin; SuperSpeed) Female
Connector Type(s)	3 - USB Type-A (9 pin) USB 3.0 Female
Connector Type(s)	1 - RJ-45 Female
Connector Type(s)	1 - 3.5 mm Mini-Jack (4 Position) Female
Connector Type(s)	1 - USB Type-B (9 pin) USB 3.0 Female
OS Compatibility	Windows® 10 (32-bit or 64-bit), 8 / 8.1 (32-bit or 64-bit), 7 (32-bit or 64-bit), Vista (32-bit or 64-bit), XP SP3 (32-bit) Mac OS® 10.6 and later (tested up to 10.11)
<b>Note</b>	HDMI and VGA adapters included VGA adapter can only be used on the DVI-I (29-pin) port
System and Cable Requirements	USB 3.0 port interface and USB 3.0 cable to connect the Laptop Docking Station to a host computer (USB 3.0 host cable included)

LED Indicators	1 - Power
Center Tip Polarity	Positive
Input Current	0.8 A
Input Voltage	100 ~ 240 AC
Output Current	4 A
Output Voltage	5 DC
Plug Type	M
Power Source	AC Adapter Included
Humidity	5~85% RH
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Cable Length	3.3 ft [1 m]
Color	Black & Silver
Enclosure Type	Aluminum and Plastic
Product Height	7 in [178 mm]
Product Length	3.3 in [83 mm]
Product Weight	10.1 oz [285 g]
Product Width	0.9 in [23 mm]
Shipping (Package) Weight	2.2 lb [1 kg]
Included in Package	1 - USB 3.0 Laptop Docking Station
Included in Package	1 - 1m USB 3.0 Cable
Included in Package	4 - Rubber Feet
Included in Package	1 - Stand
Included in Package	2 - Stand Screws
Included in Package	1 - Screwdriver
Included in Package	1 - DVI to VGA Adapter
Included in Package	1 - DVI to HDMI Adapter
Included in Package	1 - Universal Power Adapter (NA/UK/EU)
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

