

## **10-Port USB 3.0 Hub with Charge and Sync Ports - 2 x 1.5A Ports**

*StarTech ID: ST103008U2C*



This 10-port USB 3.0 hub enhances your system's capabilities by providing fast-charging for mobile devices, plus quick access to your USB devices, making it perfect for business or home-office settings.

### **Fast-charge your mobile devices**

As a charging station, the hub features two easy-access 1.5 amp charge-and-sync ports, so you can easily fast-charge your smartphones, tablets and other mobile devices. Plus, you can still connect all of your vital peripherals to the remaining data ports. Because the hub supports USB Battery Charging Specification 1.2, you can charge most mobile devices, including Apple and Samsung Galaxy™ devices.

### **Increase your productivity with ten USB 3.0 ports**

Designed for maximum scalability, this 10-port hub boosts your productivity by putting all of your USB devices within easy reach. With USB 3.0 transfer rates up to 5Gbps, it supports high-bandwidth devices such as external hard drive enclosures, flash drives, high-resolution webcams, video cameras, and more.

### **Designed for easy use**

With its sleek and compact design, you can easily position the USB 3.0 (also known as USB 3.1 Gen 1) hub on your desk or workspace to make your USB devices more accessible. There's also ample space between the USB 3.0 ports, so it's easy to plug and unplug the devices you use the most.

The USB 3.0 hub is natively supported in virtually all operating systems, which makes for an easy setup with no driver installation required.

The ST103008U2C is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Applications

- Conveniently fast-charge your mobile devices or sync with your computer
- Deploy as a charging station or data hub in hot-desk environments
- Upgrade the capabilities of your desktop or laptop with 10 additional USB 3.0 ports
- Make hard-to-reach USB ports more accessible

## Features

- Boost your system's capabilities and turn one USB 3.0 port into ten
- Fast-charge your smartphone or tablet, using two charge-and-sync ports with 1.5A output
- Charge a variety of mobile devices, including Apple and Samsung Galaxy devices, with support for USB Battery Charging Specification 1.2
- Slim and sleek black enclosure
- Built-in on/off power button
- SuperSpeed USB 3.0 throughput up to 5Gbps
- LED indicators for port status
- Plug-and-play and hot-swap compatible
- Backward compatible with USB 2.0 and 1.x devices

## Technical Specifications

|                               |                                                                                                                                                                                                                                                                                                                                                                                          |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Warranty                      | 2 Years                                                                                                                                                                                                                                                                                                                                                                                  |
| Bus Type                      | USB 3.0                                                                                                                                                                                                                                                                                                                                                                                  |
| Chipset ID                    | VLI - VL812                                                                                                                                                                                                                                                                                                                                                                              |
| Fast-Charge Port(s)           | Yes                                                                                                                                                                                                                                                                                                                                                                                      |
| Industry Standards            | USB Battery Charging Specification Rev. 1.2                                                                                                                                                                                                                                                                                                                                              |
| Industry Standards            | USB 3.0 - Backward compatible with USB 2.0/1.1                                                                                                                                                                                                                                                                                                                                           |
| Interface                     | USB 3.0                                                                                                                                                                                                                                                                                                                                                                                  |
| Ports                         | 10                                                                                                                                                                                                                                                                                                                                                                                       |
| USB-C Device Port(s)          | No                                                                                                                                                                                                                                                                                                                                                                                       |
| USB-C Host Connection         | No                                                                                                                                                                                                                                                                                                                                                                                       |
| Maximum Data Transfer Rate    | 5 Gbps                                                                                                                                                                                                                                                                                                                                                                                   |
| Type and Rate                 | USB 3.0 - 5 Gbit/s                                                                                                                                                                                                                                                                                                                                                                       |
| Connector Type(s)             | 8 - USB 3.0 A (9 pin; SuperSpeed) Female                                                                                                                                                                                                                                                                                                                                                 |
| Connector Type(s)             | 2 - USB 3.0 A (Fast-Charge; 9 pin; SuperSpeed) Female                                                                                                                                                                                                                                                                                                                                    |
| OS Compatibility              | OS Independent; No additional drivers or software required                                                                                                                                                                                                                                                                                                                               |
| <b>Note</b>                   | If connected to a USB 2.0 host port, performance may be limited                                                                                                                                                                                                                                                                                                                          |
| <b>Note</b>                   | <p><b>Charge and sync port(s) with a fast-charge icon:</b></p> <p>If your host computer is turned off, in sleep mode, or disconnected, the hub will disable data sync mode and enable fast-charge mode automatically</p> <p>If your host computer is turned on, a charge and sync port will provide a standard charge to a connected device plus simultaneous data sync capabilities</p> |
| System and Cable Requirements | Host computer with an available USB 3.0 port                                                                                                                                                                                                                                                                                                                                             |
| LED Indicators                | 10 - Port status (Blue)                                                                                                                                                                                                                                                                                                                                                                  |
| Center Tip Polarity           | Positive                                                                                                                                                                                                                                                                                                                                                                                 |
| Input Current                 | 1.5 A                                                                                                                                                                                                                                                                                                                                                                                    |
| Input Voltage                 | 100 ~ 240 AC                                                                                                                                                                                                                                                                                                                                                                             |
| Output Current                | 4 A                                                                                                                                                                                                                                                                                                                                                                                      |
| Output Voltage                | 12 DC                                                                                                                                                                                                                                                                                                                                                                                    |
| Plug Type                     | N                                                                                                                                                                                                                                                                                                                                                                                        |

|                           |                                                  |
|---------------------------|--------------------------------------------------|
| Power Consumption         | 48 W Max                                         |
| Power Source              | AC Adapter Included                              |
| Humidity                  | 10% ~ 90% RH (Non-condensing)                    |
| Operating Temperature     | 0°C to 40°C (32°F to 104°F)                      |
| Storage Temperature       | -10°C to 70°C (14°F to 158°F)                    |
| Color                     | Black                                            |
| Enclosure Type            | Plastic                                          |
| Form Factor               | Desktop                                          |
| Product Height            | 0.9 in [24 mm]                                   |
| Product Length            | 7.9 in [201 mm]                                  |
| Product Weight            | 4.9 oz [140 g]                                   |
| Product Width             | 2.4 in [60 mm]                                   |
| Shipping (Package) Weight | 1.9 lb [0.9 kg]                                  |
| Included in Package       | 1 - 10-port USB 3.0 hub with charge & sync ports |
| Included in Package       | 1 - USB 3.0 host cable                           |
| Included in Package       | 1 - universal power adapter                      |
| Included in Package       | 4 - power cords (NA/EU/UK/AU)                    |

Certifications, Reports and Compatibility

