

4 Port Black SuperSpeed USB 3.0 Hub

StarTech ID: ST4300USB3GB



The ST4300USB3GB 4-Port SuperSpeed USB 3.0 Hub allows you to add 4 additional USB 3.0 ports from a single USB 3.0 connection to the host computer system.

Backward compatible with USB 2.0 and USB 1.x standards, this USB 3.0 hub still supports older USB devices and can also be used as a hub on older systems that do not have USB 3.0 ports.

With the capability to mix and match USB 3.0/2.0/1.x devices and be used with or without the included external power adapter, this hub offers the best of versatility and portability.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Expand your USB 3.0 capabilities with additional ports
- Make hard to access USB ports more accessible by being able to position the hub anywhere the cable will reach
- Extend the range of a USB device by having the hub act as a mid-point repeater

Features

- Four USB type 'A' ports that can each be accessed simultaneously
- SuperSpeed USB 3.0 compliant, with data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.0/1.1 devices
- Supports USB 3.0/2.0/1.x devices simultaneously at full bandwidth
- Provides up to 900mA of power per port
- Compact, desktop-style form factor
- Plug-and-Play and hot-swap compatible

Technical Specifications

Warranty	2 Years
Chipset ID	VLI - VL810
Fast-Charge Port(s)	No
Interface	USB 3.0
Ports	4
USB-C Device Port(s)	No
USB-C Host Connection	No
Maximum Data Transfer Rate	5 Gbps
External Ports	1 - USB 3.0 B (9 pin; SuperSpeed) Female
External Ports	4 - USB 3.0 A (9 pin; SuperSpeed) Female
OS Compatibility	OS Independent; No additional drivers or software required
Note	If used with the Apple Mac OS operating system, this device will function in USB 2.0 mode only
System and Cable Requirements	USB 3.0 or 2.0 or 1.x compliant host controller with available port.
LED Indicators	1 - Power (Blue)
Center Tip Polarity	Positive
Input Voltage	110 ~ 240 AC
Output Current	2A
Output Voltage	5 DC
Plug Type	M
Power Source	AC Adapter Included
Humidity	5~85% RH
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Color	Black
Enclosure Type	Plastic
Form Factor	Desktop
Product Height	23 mm [0.9 in]
Product Length	95 mm [3.7 in]
Product Weight	55 g [1.9 oz]
Product Width	68 mm [2.7 in]
Shipping (Package) Weight	0.4 kg [1 lb]

Included in Package	1 - USB 3.0 Hub
Included in Package	1 - USB 3.0 cable
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

