

## **USB 2.0 to SATA/IDE Combo Adapter for 2.5/3.5" SSD/HDD**

*StarTech ID: USB2SATAIDE*



This USB 2.0 to IDE/SATA Adapter Cable connects any standard 2.5in or 3.5in SATA or IDE hard drive to a computer through USB 2.0. The adapter lets you connect a bare drive with no enclosure, saving time and hassle.

The USB 2.0 SATA/IDE Adapter features LED indicators that allow you to easily monitor status and activity updates, and is designed for durability and reliability.

### **Applications**

- Service technicians who need to test or retrieve data from old hard drives
- Technicians who travel and deal with many different types of hard drives
- Connect your 2.5" and 3.5" drives to almost any notebook or desktop
- Ideal for testing and quickly swapping drives

### **Features**

- Built in connectors for both 2.5in and 3.5in SATA and IDE hard drives
- LED indicators provide status and activity updates
- High Speed USB 2.0 host interface, with support for transfer rates up to 480 Mbps
- Compact, portable form factor

## Technical Specifications

Warranty	2 Years
Chipset ID	JMicron - JM20337
Compatible Drive Types (Type and Rate)	SATA & IDE
Drive Size	2.5in & 3.5in
Maximum Data Transfer Rate	480 Mbps
Type and Rate	USB 2.0 - 480 Mbit/s
Drive Connectors	1 - IDE (40 Pin; EIDE/PATA) Female
Drive Connectors	1 - IDE (44 Pin; EIDE/PATA; 2.5" HDD) Female
Drive Connectors	1 - LP4 (4 pin; Molex Large Drive Power) Female
Drive Connectors	1 - SATA (7 pin; Data) Plug
Drive Connectors	1 - SATA Power (15 pin) Receptacle
Host Connectors	1 - USB A (4 pin) Male
OS Compatibility	OS independent; No software or drivers required
<b>Note</b>	Backwards compatible with USB 1.1 standard, but not recommended due to slow transfer rate.
	Maximum supported drive size in Mac OSX® is 2TB
LED Indicators	1 - IDE Detect/Activity
LED Indicators	1 - SATA Detect/Activity
LED Indicators	1 - USB Link
Input Current	1A
Input Voltage	110 ~ 240 AC
Output Current	2A
Output Voltage	12/5 DC
Plug Type	Custom
Power Source	AC Adapter Included
Color	Black
Enclosure Type	Plastic
Product Height	0.6 in [15 mm]
Product Length	2.8 in [70 mm]
Product Weight	1.9 oz [54 g]
Product Width	1.7 in [43 mm]
Shipping (Package) Weight	16.1 oz [456 g]

Included in Package	1 - USB 2.0 to SATA/IDE converter
Included in Package	1 - SATA data cable
Included in Package	1 - power adapter breakout cable
Included in Package	1 - universal power adapter (NA/JP, UK, EU, AU)
Included in Package	1 - instruction manual
ATAPI Support	Yes

Certifications, Reports and Compatibility

