

RC-12S2000 - Crimp contact



1599600

<https://www.phoenixcontact.com/pc/products/1599600>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.14 mm² ... 0.56 mm², Contact release tool not necessary for the 12- and 17-pos. crimp versions of the M23-PRO series, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241093

Your advantages

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring

Commercial data

Item number	1599600
Packing unit	100 pc
Minimum order quantity	1 pc
Product key	ABREAD
Catalog page	Page 78 (C-2-2019)
GTIN	4046356226424
Weight per piece (including packing)	0.252 g
Weight per piece (excluding packing)	0.252 g
Customs tariff number	85366990
Country of origin	DE

RC-12S2000 - Crimp contact

1599600

<https://www.phoenixcontact.com/pc/products/1599600>



Technical data

Notes

Order information:	Contact release tool not necessary for the 12- and 17-pos. crimp versions of the M23-PRO series
--------------------	---

Product properties

Product type	Crimp contact
Contact material type	turned

Data management status

Article revision	02
------------------	----

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Conductor cross section	0.14 mm² ... 0.56 mm²

Material specifications

Contact surface	Nickel-plated (Ni), with gold coating (Au)
Contact material	CuZn

Dimensions

Mechanical characteristics

Contact diameter	1 mm
------------------	------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----

RC-12S2000 - Crimp contact



1599600

<https://www.phoenixcontact.com/pc/products/1599600>

Classifications

ECLASS

ECLASS-11.0	27440204
ECLASS-12.0	27440204
ECLASS-13.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

RC-12S2000 - Crimp contact



1599600
<https://www.phoenixcontact.com/pc/products/1599600>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	bfe152ca-1d8a-492e-b6d3-5958405ba47e

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com