

## PG5

ABB-Ansprechpartner für  
Deutschland

[PrintView..](#)  
[Print to Pdf..](#)

### General Information

<b>Extended Product Type:</b>	PG5
<b>Product ID:</b>	1SNK900401R0000
<b>EAN:</b>	3472599097339
<b>Catalog Description:</b>	PG5 Component Plug - Dark Grey
<b>Long Description:</b>	PG5 Component Plug - Dark Grey

### Categories

Products » Low Voltage Products and Systems » Connection Devices »  
Terminal Blocks Accessories » Component Plugs

### Ordering

<b>EAN:</b>	3472599097339
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	85369010



< 1 2 >

### Dimensions

<b>Product Net Width:</b>	5.2 mm
<b>Product Net Height:</b>	31 mm
<b>Product Net Length:</b>	39 mm
<b>Product Net Depth:</b>	39 mm
<b>Product Net Weight:</b>	3.45 g

### Container Information

<b>Package Level 1 Units:</b>	20 piece
<b>Package Level 1 Width:</b>	158 mm
<b>Package Level 1 Length:</b>	243 mm
<b>Package Level 1 Gross Weight:</b>	0.068 kg
<b>Package Level 1 EAN:</b>	3472599097339
<b>Product Packing Type:</b>	Bag

### Environmental

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

### Additional Information

<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>Color:</b>	Dark Grey
<b>Function:</b>	Component Plugs
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Insulation Material:</b>	Polyamide
<b>Medium Description:</b>	- Ease components installation ( components not supplied with plug ) with our quick plug-in mounting system (spring technology) which avoids soldering process, - Compatible with 8.8 x 3.2 mm 0.346 x 0.125 in components such as resistors or diodes, - Maximum dissipated power: 1 W.
<b>Product Main Type:</b>	PG5
<b>Product Name:</b>	Component Plugs
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	6000 V
<b>Rated Voltage (U<sub>r</sub>):</b>	400 V
<b>RoHS Date:</b>	18 08 2005
<b>Spacing:</b>	5.2 mm
<b>Sub-Function 2:</b>	Plug In

**Certificates and Declarations (Document Number)**

---

GOST Certificate: 1SND161005A1103

---

**Classifications**

---

E-nummer: 2925157

Object Classification Code: X

---