

ABS Handheld T Enclosure Black 210 x 110 x 40.5mm



DESCRIPTION

A medium-size hand-held black T case manufactured from durable high impact ABS.

DISTINCTIVE FEATURES

- Stylish, robust and ergonomic case
- Cutout areas for a display and keyboard
- Design incorporates a gasket to meet IP65 rating
- Removable tile stand or wall mounting
- Case held together by 4x M3 screws supplied
- Recessed display area 87.3 x 66.5mm
- Recessed keyboard area 105.4 x 62.7mm
- Cut-out area 72.2 x 51.5mm
- Finished in black RAL9004

APPLICATIONS

Having cutout areas for a display and keyboard makes this enclosure ideal for measuring, recording and other manual portable devices in test and measurement and data logger applications.

ABS

UL94-
HB

RAL
9004

IP65



GENERAL SPECIFICATION

Series	Handheld Enclosures
Type	T Enclosure
Screws	Qty 4 ⊕ M3 x 6mm
Internal Features	PCB Mounting
External Features	Cutouts for display & keyboard



MATERIALS

Material	ABS
Finish	Matt
Colour Including RAL Number	Black RAL9004
Screws	Zinc plated



ENVIRONMENTAL/OPERATING SPECIFICATION

Flame Resistance	UL94-HB
IP Rating	Enclosures are designed to meet the requirements of IP20 (minimum)
Operating Temperature	-20°C to +65°C




OPTIONS (MOQ may apply)

Colour	Grey RAL7035
--------	--------------



DIMENSIONS/DRAWINGS

Units	mm - unless stated otherwise
Dimensions	210 x 110 x 40.5mm
Wall Thickness	4.35mm
Weight	11g



PART NUMBER TABLE

Part Number	EAN	UNSPSC	Country of Origin
30-0397	5053556002788	39121324	Taiwan

R-TECH

Tried & trusted technology

Important Notice: This data sheet and its contents (the "Information") belong to Rapid Electronics Limited or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Rapid Electronics Limited assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Rapid Electronics Limited were aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict Rapid Electronics Limited's liability for death or personal injury resulting from its negligence.