

## Pan Head Pozidriv<sup>®</sup> Self Tapping Screw



### DESCRIPTION

Pan Head Pozidriv<sup>®</sup> Self Tapping Screws with a bright zinc-plated, passivated finish. Designed for use with sheet metal. Suitable for general use.

### DISTINCTIVE FEATURES

- Self Tapping
- Pozidriv<sup>®</sup>
- Zinc & Clear Cr3 Finish
- Hardened Steel
- Dome head style
- No.4, No.6 and No.8 options
- Supplied in packs of 100

### APPLICATIONS

Self Tapping screws are widely used in many applications to secure two materials together. Suitable for general use, typical applications include manufacturing, construction, joinery, maintenance and DIY tasks.

These self tapping screws are designed for use with sheet metal and will require a pilot hole for this purpose.

Pan head, self tapping screws are typically used for high torque applications into metal or wood and some plastics.

Pan Head

Self Tapping

Steel

Zinc & Clear Cr3





## GENERAL SPECIFICATION

Series	Self Tapping Screw
Type	PoziDriv®



## MATERIALS

Material	Steel
Finish	Zinc & Clear Cr3 De-embrittled



## CERTIFICATION AND STANDARDS

Material Specification	DIN 7981C ~ISO 7049
------------------------	---------------------





## OPTIONS (MOQ may apply)

Lengths	Various
Thread Sizes	M1.6 to M12
Thread Type	Coarse and Fine
Material	Steel
Head Styles	e.g. Button, Countersunk, Cheese, Slotted



## DIMENSIONS/DRAWINGS

Units	mm - unless stated otherwise
-------	------------------------------



Pilot Hole Information																		
Part number	Thread size	Material strength Rm (N/mm <sup>2</sup> )	Sheet metal thickness (mm)															
			1.1	1.2	1.3	1.4	1.5	1.6	1.7	1.8	1.9	2.0	2.2	2.5	2.8	3.0	3.5	
<b>33-7106</b>	2.9	> 101	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3				
<b>33-7107</b>		approx. 301	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.3	2.4	2.4	2.4					
<b>33-7108</b>		> 501	2.2	2.2	2.3	2.3	2.4	2.4	2.4	2.4	2.5	2.5	2.5					
<b>33-7109</b>	3.5	> 102			2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.8	2.9			
<b>33-7110</b>		approx. 302			2.6	2.7	2.7	2.7	2.7	2.8	2.8	2.9	2.9	3.0	3.0			
<b>33-7111</b>		> 502			2.7	2.8	2.8	2.9	2.9	2.9	2.9	3.0	3.0	3.1	3.1			
<b>33-7112</b>	4.2	> 104				3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.4	3.5	
<b>33-7113</b>		approx. 304				3.1	3.2	3.2	3.2	3.3	3.3	3.4	3.4	3.5	3.6	3.6	3.6	
<b>33-7114</b>		> 504				3.3	3.3	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.6	3.6	3.6	3.7



## PART NUMBER TABLE

Part number	A Thread size	B Length	C Screwdriver size	D Head width	E Head depth	UNSPSC	EAN	Country of Origin
<b>33-7106</b>	2.9	6.5	PZ1 - 2.9	5.6	2.20	73181499	5053556010196	China
<b>33-7107</b>		9.5				73181499	5053556010202	China
<b>33-7108</b>		13.0				73181499	5053556010219	China
<b>33-7109</b>	3.5	6.5	PZ2 - 3.9	6.9	2.6	73181499	5053556010226	China
<b>33-7110</b>		13.0				73181499	5053556010233	China
<b>33-7111</b>		19.0				73181499	5053556010240	China
<b>33-7112</b>	4.2	9.5	PZ2 - 4.3	8.20	3.05	73181499	5053556010257	China
<b>33-7113</b>		13.0				73181499	5053556010264	China
<b>33-7114</b>		19.0				73181499	5053556010271	China

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact, telephone our main office on **01206 838000** or email **Sales@Rapidonline.com**.



**Important Notice:** This data sheet and its contents (the "Information") belong to Rapid Electronics Limited or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Rapid Electronics Limited assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Rapid Electronics Limited were aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict Rapid Electronics Limited's liability for death or personal injury resulting from its negligence.