


UK +44 (0)151 220 2500 // USA +1 855 958 2502 // www.brainboxes.com // sales@brainboxes.com

US-720

USB-C to 1 Port 422/485 Industrial USB to Serial Adaptor

- Our smallest form factor USB-C to serial adaptor
- High retention USB connector for an unshakeable connection
- Comes with 1m USB-B to USB-C cable
- Works where many other USB to Serial devices do not
- Industrial Specification: IP-50
- -40°C to +80°C/-40°F to +176°F



IP-50 rated non-conducting case



Wall mounting option



High retention USB connection requires a minimum withdrawal requirement of 15N (thats a force of 1.5Kg or 3.4lbs)

UK +44 (0)151 220 2500 // USA +1 855 958 2502 //
www.brainboxes.com // sales@brainboxes.com

US-720 USB-C to 1 Port 422/485 Industrial USB to Serial Adaptor

IP-50 rated non-conducting case

High retention USB connector for an unshakeable connection

Plug and play with signed drivers

Orange color-coded insulator to differentiate from standard USB connectors

-40°C to +80°C/-40°F to +176°F temperature range

USB connection requires a minimum withdrawal requirement of 15N

Wall mounting option



Works across the full spectrum of baud rates up to 921,600 including standard and arbitrary values

Housing & Connectors

IP-50 rated non-conducting polyamide case
DB9 Connector - 9 Pin Male
High Retention USB Connector
Wall mounting screw recess

Power Supply

Power Supply Input +5V through USB cable (supplied)
Power Consumption 50mA @ 5V

Environmental


Operating Temperature -40°C to +80°C/-40°F to +176°F
Storage Temperature -40°C to +80°C/-40°F to +176°F

Port Settings - RS232

Baud Rate From 110 - 1 MegaBaud - Any custom Baud rate accepted
Data Bits 5,6,7 or 8
Parity Odd, Even, None, Mark or Space
Stop Bits 1 or 2
Flow Control RTS/CTS, DSR/DTR, XON/XOFF
Tx/Rx Modes Point to Point

UK +44 (0)151 220 2500 // USA +1 855 958 2502 // www.brainboxes.com // sales@brainboxes.com



US-720 USB-C to 1 Port 422/485 Industrial USB to Serial Adaptor




RS422/485

| | |
|-------|-------|
| Pin 1 | TXD- |
| Pin 2 | TXD+ |
| Pin 3 | RTS- |
| Pin 4 | RTS+ |
| Pin 5 | GND |
| Pin 6 | RXD- |
| Pin 7 | RXD+ |
| Pin 8 | CTS - |
| Pin 9 | CTS+ |

RS422/485 Pinout (9 Pin)



HIGH RETENTION SOCKET
(min withdrawal 15N)



USB-B plug

USB-C plug

connect to phones/tablets/PCs

Software

OS Compatibility

Microsoft

Brainboxes' software provides a TCP or Serial COM port interface. All software versions and updates available to download from our website.

Windows 8, Windows 8.1, Windows 10
Windows Server 2016
Windows Server 2019



Lifetime Warranty and Support:

We can help with every aspect of your project, from getting you up and running to custom application.

UK +44 (0)151 220 2500 // USA +1 855 958 2502 // www.brainboxes.com // sales@brainboxes.com

US-720 USB-C to 1 Port 422/485 Industrial USB to Serial Adaptor

| | |
|-------------------------|---|
| Packaging Information | QSG, Device, USB-C Cable (signed drivers are automatically downloaded by Windows OS) |
| Product Weight | 0.024 kg, 0.85 ounces |
| Product Dims | 41x38x22 mm, 1.6x1.5x0.9 inches |
| Packaged Weight | 0.155 kg, 5.47 ounces |
| Packaged Dims | 160x135x45 mm, 6.3x5.3x1.8 inches |
| GTIN Universal Code | 837324004618 |
| Industry Approvals | Microsoft Certified Gold Partner, WEEE, RoHS, AEO (C-TPAT), CE, UKCA |
| HTS | 8471800000 |
| ECCN | 49449A |
| CAGE | 8QCY6 |
| Warranty | Lifetime - online registration required |
| Support | Lifetime Web, Email & Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team |
| Standards | ISO9001, ISO14001 |
| OEM option | Available for bulk buy OEM |
| COO (Country of Origin) | GB |
| Made In | Manufactured in GB by Brainboxes |
| Customisable | Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users More info: sales@brainboxes.com |

USB-C Range

USB-C adaptors available in a range of formats and specifications

www.brainboxes.com



US-735

USB-C to 1 Port
RS232 Industrial USB to
Serial Adaptor



US-757

USB-C to 2 Port
RS232 Serial Server Hub



US-759

USB-C to 1 Port
RS232 Industrial Isolated
USB to Serial Adaptor