



| | | | |
|---------------------|---------------|-------------------------------|-----------|
| EAN/GTIN: | 4013288016225 | Dimension: | 70x7x6 mm |
| Part no.: | 05060125001 | Weight: | 15 g |
| Article no.: | 867/4 Z TORX® | Country of origin: | CZ |
| | | Customs tariff number: | 82079030 |

- For recessed TORX® screws
- Ductile and tough for hard materials
- 1/4" hexagon drive
- Suitable for AEG, ARO, Atlas-Copco, Biax, Black & Decker, Bosch, Buckeye Tools etc.
- Prevents premature breakage of the drive tip

High quality bits for recessed TORX® screws. Tough viscous for universal use. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_wera_bits_bits_for_torx_screws_867_4_z_torx.html

Wera - 867/4 Z TORX®
05060125001 - 4013288016225

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de





Bits for TORX® Screws

Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

More variants of this product family:

| |  |  mm |  inch |  mm |
|-------------|---|---|---|---|
| 05135200001 | TX 1 | 50 | 2 | 2.0 |
| 05135201001 | TX 2 | 50 | 2 | 2.0 |
| 05135202001 | TX 3 | 50 | 2 | 2.0 |
| 05135204001 | TX 4 | 50 | 2 | 3.0 |
| 05135205001 | TX 5 | 50 | 2 | 3.0 |
| 05308428001 | TX 6 | 50 | 2 | 3.0 |
| 05134740001 | TX 6 | 70 | 2 3/4 | 3.0 |
| 05332600001 | TX 6 | 89 | 3 1/2 | 3.0 |
| 05328448001 | TX 6 | 152 | 6 | 3.0 |
| 05160830001 | TX 7 | 50 | 2 | 3.0 |
| 05345047001 | TX 7 | 70 | 2 3/4 | 3.0 |
| 05060131001 | TX 8 | 50 | 2 | 3.0 |
| 05060098001 | TX 8 | 70 | 2 3/4 | 3.0 |
| 05060185001 | TX 8 | 89 | 3 1/2 | 3.0 |
| 05060195001 | TX 8 | 152 | 6 | 3.0 |
| 05319835001 | TX 9 | 70 | 2 3/4 | 3.0 |
| 05060193001 | TX 9 | 89 | 3 1/2 | 3.0 |
| 05060194001 | TX 9 | 152 | 6 | 3.0 |
| 05060132001 | TX 10 | 50 | 2 | 4.0 |
| 05060100001 | TX 10 | 70 | 2 3/4 | 4.0 |
| 05060186001 | TX 10 | 89 | 3 1/2 | 4.0 |
| 05060196001 | TX 10 | 152 | 6 | 4.0 |

Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_wera_bits_bits_for_torx_screws_867_4_z_torx.html

Wera - 867/4 Z TORX®
 05060125001 - 4013288016225

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Bits for TORX® Screws

| | | | | |
|--------------------|--------------|-----------|--------------|------------|
| 05060133001 | TX 15 | 50 | 2 | 4.0 |
| 05060105001 | TX 15 | 70 | 2 3/4 | 4.0 |
| 05060187001 | TX 15 | 89 | 3 1/2 | 4.0 |
| 05060197001 | TX 15 | 152 | 6 | 4.0 |
| 05060134001 | TX 20 | 50 | 2 | 4.5 |
| 05060110001 | TX 20 | 70 | 2 3/4 | 4.5 |
| 05060188001 | TX 20 | 89 | 3 1/2 | 4.5 |
| 05060198001 | TX 20 | 152 | 6 | 4.5 |
| 05060135001 | TX 25 | 50 | 2 | 6.0 |
| 05060115001 | TX 25 | 70 | 2 3/4 | 6.0 |
| 05060189001 | TX 25 | 89 | 3 1/2 | 6.0 |
| 05060199001 | TX 25 | 152 | 6 | 6.0 |
| 05060136001 | TX 27 | 50 | 2 | 6.0 |
| 05060120001 | TX 27 | 70 | 2 3/4 | 6.0 |
| 05060190001 | TX 27 | 89 | 3 1/2 | 6.0 |
| 05060200001 | TX 27 | 152 | 6 | 6.0 |
| 05060137001 | TX 30 | 50 | 2 | 6.0 |
| 05060125001 | TX 30 | 70 | 2 3/4 | 6.0 |
| 05060191001 | TX 30 | 89 | 3 1/2 | 6.0 |
| 05060201001 | TX 30 | 152 | 6 | 6.0 |
| 05060138001 | TX 40 | 50 | 2 | - |
| 05060130001 | TX 40 | 70 | 2 3/4 | - |
| 05060192001 | TX 40 | 89 | 3 1/2 | - |
| 05060202001 | TX 40 | 152 | 6 | - |

Weblink

http://products.wera.de/en/tools_for_the_aerospace_segment_wera_bits_bits_for_torx_screws_867_4_z_torx.html

Wera - 867/4 Z TORX®
 05060125001 - 4013288016225

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de