

## Product information

# 97 90 12

## Crimp Assortment

For wire ferrules

- With Self-Adjusting Insulation Stripper 12 40 200
- With Self-Adjusting Crimping Pliers for wire ferrules 97 53 08
- In a TANOS MINI-systainer® (solid plastic box)
- T-Loc fastener for one-handed operation: open or close the systainer® with one turn and connect to a second systainer®
- Opening when connected: fast and simple access to content without disconnecting
- Two stackable plastic inserts with 6 trays each for connectors
- With an assortment of wire ferrules with/without collar




### General

|             |               |
|-------------|---------------|
| Article No. | 97 90 12      |
| EAN         | 4003773048916 |
| weight      | 1,427 g       |
| Dimensions  | 170 x 69 mm   |
| Reach       | yes           |
| RohS        | no            |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 27400218   |
| ETIM 5.0       | EC000524   |
| ETIM 6.0       | EC000524   |
| proficl@ss 6.0 | EAB559c013 |
| UNSPSC 13.1    | 27112147   |

### Content

|           |  |
|-----------|--|
| 12 40 200 | 1 x Self-Adjusting Insulation Stripper (0,03 – 10,0 mm <sup>2</sup> )<br>MM  |
| 97 53 08  | 1 x Self-Adjusting Crimping Pliers for wire ferrules with front loading (0,08 – 10 mm <sup>2</sup> )<br>MM  |
|           | 50 x Wire ferrules with plastic collar 14 / 8 mm (0,5 mm <sup>2</sup> )  |
|           | 100 x Wire ferrules with plastic collar 14 / 8 mm (0,75 mm <sup>2</sup> )  |
|           | 100 x Wire ferrules with plastic collar 14 / 8 mm (1 mm <sup>2</sup> )   |
|           | 200 x Wire ferrules with plastic collar 14 / 8 mm (1,5 mm <sup>2</sup> )   |
|           | 200 x Wire ferrules with plastic collar 14 / 8 mm (2,5 mm <sup>2</sup> )   |
|           | 200 x Wire ferrules with plastic collar 17 / 10 mm (4 mm <sup>2</sup> )  |
|           | 200 x Wire ferrules with plastic collar 20 / 12 mm (6 mm <sup>2</sup> )  |

## Content

|  |
|--|
| 200 x Wire ferrules with plastic collar 22 / 12 mm (10 mm <sup>2</sup> ) |
|--|

*technical change and errors excepted*

*Systemer® is a registered trademark of TANOS GmbH*

