

## Kraftform Kompakt 60, stainless, 17 pieces

Kraftform Kompakt 60, 62



<b>EAN/GTIN:</b>	4013288115713	<b>Dimension:</b>	155x130x55 mm
<b>Part no.:</b>	05071116001	<b>Weight:</b>	534 g
<b>Article no.:</b>	KK 60 Stainless	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82079030

- Solution to the extraneous rust problem: fasten stainless screws with stainless tools
- Vacuum ice-hardening provides the required hardness and strength
- Handle/Interchangeable blade system for rapid exchange of the blade
- Rapidaptor technology for rapid bit change
- Storage and transport in a robust belt pouch

Pouch with bits in a length of 89 mm. Includes Kraftform holder 3816 R with Rapidaptor quick-release chuck and multi-component Kraftform handle for low-fatigue working. Stainless design to prevent the formation of extraneous rust.







### Weblink

[http://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_60\\_62\\_kk\\_60\\_stainless.html](http://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_stainless.html)

Wera - KK 60 Stainless  
05071116001 - 4013288115713

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

### Content:



### Screw stainless steel together with stainless steel!



Solution to the rust problem: screw stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of stainless steel so unsightly rust can be avoided.

### Vacuum ice-hardened



The stainless steel tools from Wera are vacuum ice-hardened and have the hardness and strength needed for screw connections. There are no limitations to the industrial applications they are suitable for.

### Handle/interchangeable blade system



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

### Chuck-all



The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.


### Weblink

[http://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_60\\_62\\_kk\\_60\\_stainless.html](http://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_stainless.html)

Wera - KK 60 Stainless  
05071116001 - 4013288115713


Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**Rapid-in and self-lock**



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

**Rapid-out**




Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

**Prevents hand injuries**



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

**Storage and transport**



The tools can be stored and carried in a robust belt pouch, keeping them always to hand.

**Weblink**

[http://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_60\\_62\\_kk\\_60\\_stainless.html](http://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_stainless.html)

Wera - KK 60 Stainless  
05071116001 - 4013288115713