



2-conductor center terminal block; required between end plate and end terminal block for terminal strips with fixing flanges; suitable for Ex i applications

Item No.: 264-324



2-conductor center terminal block; required between end plate and end terminal block for terminal strips with fixing flanges; suitable for Ex i applications

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	264-324
GTIN / EAN	4044918415293
Content	1

Notes

Technical data

Miscellaneous


Rated voltage (III / 3) [V]	800 [V]
Rated impulse voltage (III / 3) [kV]	8 [kV]
Rated current [A]	24 [A]
Legend (ratings)	(III / 3) Overvoltage category III / Pollution degree 3
Connection technology	CAGE CLAMP®

Printview: 2-conductor center terminal block; required between end plate and end terminal block for terminal strips with fixing flanges; suitable for Ex i applications - Item No.: 264-324

Technical data	
<i>Actuation type</i>	<i>Operating tool</i>
<i>Connectable conductor materials</i>	<i>Copper</i>
<i>Solid conductor</i>	<i>0.08 ... 2.5 mm² / 28 ... 12 AWG</i>
<i>Fine-stranded conductor</i>	<i>0.08 ... 2.5 mm² / 28 ... 12 AWG</i>
<i>Strip length</i>	<i>8 ... 9 mm / 0.31 ... 0.35 Inch</i>
<i>Total number of connection points</i>	<i>2</i>
<i>Total number of potentials</i>	<i>1</i>
<i>Number of levels</i>	<i>1</i>
<i>Type of wiring</i>	<i>Front-entry wiring</i>
<i>Note (conductor cross-section)</i>	<i>12 AWG: THHN, THWN</i>
<i>Width</i>	<i>6 mm / 0.236 Inch</i>
<i>Height from the surface</i>	<i>22.1 mm / 0.87 Inch</i>
<i>Depth</i>	<i>32 mm / 1.26 Inch</i>
<i>Design</i>	<i>horizontal</i>
<i>Mounting type</i>	<i>Mounting flange</i>
<i>Marking level</i>	<i>Center marking</i>
<i>Color</i>	<i>blue</i>
<i>Fire load [MJ]</i>	<i>0.074 [MJ]</i>
<i>Weight [g]</i>	<i>3.825 [g]</i>
<i>Packaging type</i>	<i>BOX</i>
<i>Main product function</i>	<i>Through term. block</i>
<i>Product type</i>	<i>Miniature rail-mount terminal blocks</i>

Printview: 2-conductor center terminal block; required between end plate and end terminal block for terminal strips with fixing flanges; suitable for Ex i applications - Item No.: 264-324

Images & drawings



Printview: 2-conductor center terminal block; required between end plate and end terminal block for terminal strips with fixing flanges; suitable for Ex i applications - Item No.: 264-324



Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.