



**4-conductor double deck terminal block; 8-conductor ground terminal block; PE; without marker carrier; green-yellow housing; internal commoning**

*Item No.: 2002-2407*



## Marking

RoHS ✓  
Compliant

## Business data

<i>Supplier</i>	WAGO
<i>Item no.</i>	2002-2407
<i>GTIN / EAN</i>	4050821145004
<i>Content</i>	1
<i>Order amount</i>	1

## Notes

## Technical data



### Miscellaneous



<i>Ratings per</i>	IEC/EN 60947-7-2
<i>Type of wiring</i>	Front-entry wiring
<i>Total number of connection points</i>	8
<i>Total number of potentials</i>	1

Printview: 4-conductor double deck terminal block; 8-conductor ground terminal block; PE; without marker carrier; green-yellow housing; internal commoning - Item No.: 2002-2407

<b>Technical data</b>	
<i>Number of levels</i>	2
<i>Connection technology</i>	Push-in CAGE CLAMP®
<i>Actuation type</i>	Push-in
<i>Connectable conductor materials</i>	Copper
<i>Nominal cross section</i>	2.5 mm <sup>2</sup>
<i>Solid conductor</i>	0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG
<i>Solid conductor, push-in termination</i>	0.75 ... 4 mm <sup>2</sup> / 18 ... 12 AWG
<i>Fine-stranded conductor</i>	0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG
<i>Fine-stranded conductor with ferrule, push-in termination, f</i>	0.75 mm <sup>2</sup> / 18 AWG
<i>Strip length</i>	10 ... 12 mm / 0.39 ... 0.47 Inch
<i>Width</i>	5.2 mm / 0.205 Inch
<i>Height from upper-edge of DIN-35 rail</i>	52.1 mm / 2.051 Inch
<i>Depth</i>	105.1 mm / 4.138 Inch
<i>Design</i>	horizontal
<i>Type of mounting</i>	Carrier rail 35 x 15
<i>Potential marking</i>	PE
<i>Marking level</i>	Center/side marking
<i>Color</i>	green-yellow
<i>Insulating material</i>	Polyamide 66 (PA 66)
<i>Fire load [MJ]</i>	0.282 [MJ]
<i>Weight [g]</i>	18.85 [g]
<i>Product Family</i>	TOPJOB® S
<i>Main product function</i>	Multilevel terminal blocks
<i>Product type</i>	Through rail-mount term. blocks

Images & drawings





**Address**

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.