

HAND HELD CASES

80 Series Slim Plastic Enclosures

Small ABS hand-held enclosures, with battery compartment and rubber boot options.

- Moulded in UL94-HB ABS
- Lid mounted by four self-tapping screws
- Sliding battery compartment lid options for a CR 2032 battery (contacts included)
- Three sizes available
- Optional rubber case, open or closed variations
- Recess in base for product labels, keyboards and overlays

SPECIFICATION

Material	Lid & base in UL94-HB ABS
Operating Temperature	-10°C to +60°C
Standard colours	Black or white
Standard unit includes	Lid, base & battery-lid 4x M1.6 Steel screws Battery contact
Options	Rubber boot PCB

TAKACHI



Without Battery Compartment

BLACK	WHITE	LENGTH	WIDTH	HEIGHT	DESCRIPTION
CHH801NBK	CHH801NWH	75mm	35mm	12mm	No battery compartment
CHH802NBK	CHH802NWH	90mm	45mm	12mm	No battery compartment
CHH803NBK	CHH803NWH	115mm	63mm	12mm	No battery compartment

With Battery Compartment

BLACK	WHITE	LENGTH	WIDTH	HEIGHT	DESCRIPTION
CHH801BBK	CHH801BWH	75mm	35mm	12mm	1x CR 2032 Battery compartment
CHH802BBK	CHH802BWH	90mm	45mm	12mm	1x CR 2032 Battery compartment
CHH803BBK	CHH803BWH	115mm	63mm	12mm	2x CR 2032 Battery compartment

Rubber Boots



- Flexible open faced removable silicon rubber boot
- Fits tightly over base, sides and around edges of lid
- Available in three sizes, in black, blue and yellow




Rubber Boots

PART NO.	LENGTH	WIDTH	HEIGHT	DESCRIPTION
CHH80BABK	78.6mm	38.6mm	15.5mm	RUBBER CASE, SIZE 1, CLOSED, BLACK
CHH80BBBK	78.6mm	38.6mm	15.5mm	RUBBER CASE, SIZE 1, OPEN, BLACK
CHH80BABL	78.6mm	38.6mm	15.5mm	RUBBER CASE, SIZE 1, CLOSED, BLUE
CHH80BBBL	78.6mm	38.6mm	15.5mm	RUBBER CASE, SIZE 1, OPEN, BLUE
CHH80BAYL	78.6mm	38.6mm	15.5mm	RUBBER CASE, SIZE 1, CLOSED, YELLOW
CHH80BBYL	78.6mm	38.6mm	15.5mm	RUBBER CASE, SIZE 1, OPEN, YELLOW
CHH80BCBK	93.6mm	48.6mm	15.5mm	RUBBER CASE, SIZE 2, CLOSED, BLACK
CHH80BDBK	93.6mm	48.6mm	15.5mm	RUBBER CASE, SIZE 2, OPEN, BLACK
CHH80BCBL	93.6mm	48.6mm	15.5mm	RUBBER CASE, SIZE 2, CLOSED, BLUE
CHH80BDBL	93.6mm	48.6mm	15.5mm	RUBBER CASE, SIZE 2, OPEN, BLUE
CHH80BCYL	93.6mm	48.6mm	15.5mm	RUBBER CASE, SIZE 2, CLOSED, YELLOW
CHH80BDYL	93.6mm	48.6mm	15.5mm	RUBBER CASE, SIZE 2, OPEN, YELLOW
CHH80BEBK	119.1mm	67.1mm	16mm	RUBBER CASE, SIZE 3, CLOSED, BLACK
CHH80BFBK	119.1mm	67.1mm	16mm	RUBBER CASE, SIZE 3, OPEN, BLACK
CHH80BEBL	119.1mm	67.1mm	16mm	RUBBER CASE, SIZE 3, CLOSED, BLUE
CHH80BFBL	119.1mm	67.1mm	16mm	RUBBER CASE, SIZE 3, OPEN, BLUE
CHH80BEYL	119.1mm	67.1mm	16mm	RUBBER CASE, SIZE 3, CLOSED, YELLOW
CHH80BFYL	119.1mm	67.1mm	16mm	RUBBER CASE, SIZE 3, OPEN, YELLOW

HAND HELD CASES

PCB



- Exclusive PCB board for the Slim plastic enclosure
- Glass epoxy board (FR-4), through-holes on both sides and 2.54mm hole distance
- Prepared holes for the battery contact

PCB

PART NO.	LENGTH	WIDTH	HEIGHT	DESCRIPTION
CHH80PCB1	68.9mm	28.9mm	1mm	PCB board for size 1 Enclosure
CHH80PCB2	83.9mm	38.9mm	1mm	PCB board for size 2 Enclosure
CHH80PCB3	108.9mm	56.9mm	1mm	PCB board for size 3 Enclosure

Wrist Straps



PINK	YELLOW	GREEN	BLUE	LIGHT GREY	BLACK	LENGTH	WIDTH
CHHWRSTPK	CHHWRSTYL	CHHWRSTGR	CHHWRSTBL	CHHWRSTLG	CHHWRSTBK	140mm	8mm

- Wrist straps for the Slim plastic enclosure, come in six colours pink, yellow, green, blue, grey and black.

Neck Straps



PINK	YELLOW	GREEN	BLUE	LIGHT GREY	BLACK	LENGTH	WIDTH
CHHNECKPK	CHHNECKYL	CHHNECKGR	CHHNECKBL	CHHNECKLG	CHHNECKBK	450mm	10mm

- Neck straps for the Slim plastic enclosure, come in six colours pink, yellow, green, blue, grey and black.
- Neck strap comes with a quick release joint



UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

19" CABINETS

DEVELOPMENT BOARDS

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES



+44 (0)1638 716101
info@camdenboss.com
www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1.0

CAMDENBOSS
ELECTRONICS & ENCLOSURES